

SIRIUS SAFETY RELAY SAFETY-RELATED SPEED MONITORING, 110 - 240 V AC/DC, 45.0 MM, SCREW CONNECTION, ENABLING CIRCUIT INSTANTANEOUS:2NO, ENABLING CIRCUIT DELAYED: 0, SIGNALING CIRCUIT: 2 ELECTRICAL, NAMUR VERSION AUTO START / MANUAL START, BASIC UNIT, MAX. ERR. PL EN13849-1: E, MAX. ERR. SIL TO IEC61508: 3,

General technical data:

product brand name		SIRIUS
Product designation		safety relays
Design of the product		standstill and speed monitoring
Protection class IP of the enclosure		IP20
Protection class IP of the terminal		IP20
Protection against electrical shock		finger-safe
Insulation voltage Rated value	V	300
Ambient temperature		
• during storage	°C	-20 ... +70
• during operation	°C	0 ... 60
Air pressure acc. to SN 31205	kPa	90 ... 106
Relative humidity during operation	%	10 ... 95
Installation altitude at height above sea level maximum	m	2 000
Vibration resistance acc. to IEC 60068-2-6		10 ... 55 Hz: 0.35 mm
Shock resistance		8g / 10 ms
Surge voltage resistance Rated value	V	4 000
EMC emitted interference		EN 60947-5-1
Installation environment regarding EMC		This product is suitable for Class A environments only. It can cause undesired radio-frequency interference in residential environments. If this is the case, the user must take appropriate measures.
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		KT
Equipment marking acc. to DIN EN 61346-2		F

Number of sensor inputs		
• 2-channel		3
• 1-channel or 2-channel		0
Design of the cascading		none
Type of the safety-related wiring of the inputs		single-channel or two-channel
Product property cross-circuit-proof		Yes
Safety Integrity Level (SIL)		
• acc. to IEC 61508		SIL3
• for delayed release circuit acc. to IEC 61508		SIL3
SIL Claim Limit (subsystem) acc. to EN 62061		3
Performance level (PL)		
• acc. to EN ISO 13849-1		e
• for delayed release circuit acc. to EN ISO 13849-1		e
Category acc. to EN 954-1		4
Category acc. to EN ISO 13849-1		4
Hardware fault tolerance acc. to IEC 61508		1
Safety device type acc. to IEC 61508-2		Type B
PFHD with high demand rate acc. to EN 62061	1/h	0.0000000034
T1 value for proof test interval or service life acc. to IEC 61508	y	20
Number of outputs as contact-affected switching element		
• as NC contact		
— for signaling function instantaneous contact		0
— for signaling function delayed switching		0
— safety-related instantaneous contact		0
— safety-related delayed switching		0
• as NO contact		
— for signaling function instantaneous contact		0
— for signaling function delayed switching		0
— safety-related instantaneous contact		1
— safety-related delayed switching		1
Number of outputs as contact-less semiconductor switching element		
• safety-related		
— delayed switching		0
— instantaneous contact		0
• for signaling function		
— delayed switching		1
— instantaneous contact		1

Stop category acc. to DIN EN 60204-1	0
--------------------------------------	---

General technical data:

Design of input		
• cascading input/functional switching		No
• feedback input		Yes
• Start input		Yes
Type of electrical connection Plug-in socket		Yes
Switching capacity current		
• of semiconductor outputs		
— for signaling function at DC-13 at 24 V	A	0.02
• of the NO contacts of the relay outputs		
— at DC-13		
— at 24 V	A	2
— at AC-15		
— at 24 V	A	3
— at 230 V	A	3
• of the NC contacts of the relay outputs		
— at AC-15		
— at 24 V	A	3
— at 115 V	A	3
— at 230 V	A	2
Thermal current of the switching element with contacts maximum	A	5
Electrical endurance (switching cycles) typical		100 000
Mechanical service life (switching cycles) typical		50 000 000
Design of the fuse link for short-circuit protection of the NO contacts of the relay outputs required		gL/gG: 4 A

Control circuit/ Control:

Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency		
• 1 Rated value	Hz	50
• 2 Rated value	Hz	60
Control supply voltage 1		
• for DC	V	110 ... 240
Control supply voltage 1 with AC		
• at 50 Hz	V	110 ... 240
• at 60 Hz	V	110 ... 240
Operating range factor control supply voltage rated value of the magnet coil		
• with AC		
— at 50 Hz		0.8 ... 1.1
— at 60 Hz		0.8 ... 1.1

- for DC

0.8 ... 1.1

Installation/ mounting/ dimensions:

mounting position		any
Mounting type		screw and snap-on mounting
Width	mm	45
Height	mm	105.9
Depth	mm	124.3

Connections/ Terminals:

Type of electrical connection		screw-type terminals
Type of connectable conductor cross-section		0.5 ... 4 mm ²
<ul style="list-style-type: none"> • solid • finely stranded — with core end processing 		1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²)
Type of connectable conductor cross-section for AWG conductors		
<ul style="list-style-type: none"> • solid • stranded 		2x (20 ... 14) 2x (20 ... 14)

Product Function:

Product function		
<ul style="list-style-type: none"> • Light barrier monitoring • Standstill monitoring • protective door monitoring • Automatic start • magnetically operated switch monitoring NC-NO • rotation speed monitoring • laser scanner monitoring • monitored start-up • Light array monitoring • magnetically operated switch monitoring NC-NC • EMERGENCY OFF function • Pressure-sensitive mat monitoring 		No Yes Yes Yes No Yes No Yes No No Yes No
Suitability for interaction press control		No
Suitability for use		
<ul style="list-style-type: none"> • Monitoring of floating sensors • Monitoring of non-floating sensors • safety switch • position switch monitoring • EMERGENCY-OFF circuit monitoring • valve monitoring 		Yes No Yes Yes No No

- tactile sensor monitoring
- magnetically operated switch monitoring
- safety-related circuits

	No
	No
	Yes

Certificates/ approvals:

Certificate of suitability

- TÜV (German technical inspectorate) certificate
- UL approval
- BG BIA certificate

	TÜV / IEC 61508
	Yes
	Yes
	No

General Product Approval

Functional
Safety/Safety
of Machinery



CCC



CSA



TÜV



UL



[Type Examination](#)

Declaration of
Conformity

other



EG-Konf.

[Declaration of
Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TK28101KA410AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TK28101KA410AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TK28101KA410AA0&lang=en



last modified:

16.03.2015