Connection Line M12 × 1; 4-pin

ZAS02V802

Part Number







Technical Data

Mechanical Data				
Connection 1	1 Socket, angled			
Connection mode 1	M12 × 1, 4-pin			
Connection 2	stripped			
Torque	M12: 0,7 Nm			
Cable Length	25 m			
Cable Diameter	5 mm			
Wire cross-section	0,25 mm ²			
Display	LED			
Degree of Protection	IP68/IP69K			
Temperature Range	-2570 °C			
Cable Jacket Material	PVC			
Material Wire Insulation	PVC			
Material Sleeve Nut	Stainless Steel 316L			
Packaging unit	1 Piece			
Connection Diagram No.	S03			
Connection Equipment No.	2			

- Protection mode IP69K
- With LED, angled





Leger	nd	PT	Platinum measuring resistor	ENARSAS	Encoder A/Ā (TTL)	
+	Supply Voltage +	nc	not connected	ENBR542	Encoder B/B (TTL)	
-	Supply Voltage 0 V	U	Test Input	ENA	Encoder A	
~	Supply Voltage (AC Voltage)	Ū	Test Input inverted	ENв	Encoder B	
Α	Switching Output (NO)	W	Trigger Input	Амін	Digital output MIN	
Ā	Switching Output (NC)	W-	Ground for the Trigger Input	Амах	Digital output MAX	
V	Contamination/Error Output (NO)	0	Analog Output	Аок	Digital output OK	
⊽	Contamination/Error Output (NC)	0-	Ground for the Analog Output	SY In	Synchronization In	
E	Input (analog or digital)	BZ	Block Discharge	SY OUT	Synchronization OUT	
Т	Teach Input	Amv	Valve Output	OLT	Brightness output	
Z	Time Delay (activation)	а	Valve Control Output +	М	Maintenance	
S	Shielding	b	Valve Control Output 0 V	rsv	reserved	
RxD	Interface Receive Path	SY	Synchronization		Wire Colors according to DIN IEC 757	
TxD	Interface Send Path	SY-	 Ground for the Synchronization 	n BK	Black	
RDY	Ready	E+	Receiver-Line	BN	Brown	
GND	Ground	S+	Emitter-Line	RD	Red	
CL	Clock	+	Grounding	OG	Orange	
E/A	Output/Input programmable	SnR	Switching Distance Reduction	YE	Yellow	
②	IO-Link	Rx+	-/- Ethernet Receive Path	GN	Green	
PoE	Power over Ethernet	Tx+	-/- Ethernet Send Path	BU	Blue	
IN	Safety Input	Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
OSSD	Safety Output	La	Emitted Light disengageable	GY	Grey	
Signal	Signal Output	Mag	Magnet activation	WH	White	
BI_D+/-	Ethernet Gigabit bidirect. data line (A			PK	Pink	
	Encoder 0-pulse 0-Ō (TTL)	EDM		GNYE	Green/Yellow	