Belden

TECHNICAL DATA SHEET

concept

code version 1

date 2004-04-27

page 1/2

4500FE NON-PAIRED

APPLICATION

Intercom/PA Systems, Sound/Audio Systems.

CONSTRUCTION



1. Conductor

Diameter of conductor 0.75mm (AWG22)

Material stranded bare copper (7xAWG30)

2. Insulation

Material PE

Diameter over insulation $1.25 \pm 0.05 \text{ mm}$ Wallthickness 0.25 mm

3. Overall Cabling

Colour code black-red

4. Outer shield

Shield Beldfoil®)

Shield Material Aluminium / Polyester tape

Shield Thickness Alu 9 μm Shield coverage 100%

Drainwire AWG24 (7xAWG32) tinned Cu

4. Sheath

REQUIREMENTS AND TEST METHODS

Electrical:

Nominal resistance conductor 54 Ω /km Nominal resistance shield 54 Ω /km Nom. capacitance conductor to conductor @ 1kHz 150 pF/m Nom. capacitance cond. to shield + other cond. @ 1kHz 285 pF/m

Testvoltage conductor-conductor 2500 VDC, 3 seconds Testvoltage conductor-screen 2500 VDC, 3 seconds

Voltage rating 300 V RMS

Maximum continues current per conductor @ 25 °C 2.8 A per conductor @ 25 °C



TECHNICAL DATA SHEET

concept

code

version 1 date 2004-04-27

page 2/2

4500FE NON-PAIRED

Mechanical and physical:

Temperature range processing and operating -20 to +70 °CTemperature range storage -30 to +70 °CMinimum bending/setting radius 5*D/10*DMaximum pulling tension 11 N

Halogen free according to IEC 60754-1

Non dense smoke according to IEC 61034-1 and 61034-2

Non corrosive gas according to IEC 60754-2 Flame Retardant according to IEC 60332-1

MARKING

NEW GENERATION(R) BY BELDEN 4500FE HALOGEN FREE 70C 2C22 SHIELDED + sequential meter marking.