

## Cutter for circular cutter, type 422

### Application:

For use in a circular cutter, type 00 and 00a, with drawing cut for sheet metal, steel and non-ferrous metals with a max. cutting depth of 5 mm.



<b>Art. no.</b>	<b>11373 141</b>
<b>Brand</b>	GFS
<b>Manufacturer Part Number</b>	22 011 142
<b>Form</b>	422
<b>Suitable for type</b>	00, 00 a
<b>Cutting material</b>	Carbide
<b>Surface</b>	Uncoated
<b>Gross Weight</b>	0.012 kg
<b>Product Group</b>	119