


RFNA4JGILGIE Datasheet

Product Name // N Jack Straight 4 Hole Flange RF Connector

[View Product Page](#)



// Product Description:	
<ul style="list-style-type: none"> N Jack Straight 4 Hole Flange RF Connector Maximum Voltage: 500V Temperature range: -55Å°C to +155Å°C Frecuency range: 0GHz - 18GHz VSWR: 	<ul style="list-style-type: none"> Dielectric withstanding Voltage: >1500V Impedance: 50Ohm Body Material: Stainless Steel Passivation Contact Material: Beryllium Copper

// General Information:	
Product Display Title:	N Type Series Pin with Extended PTFE 4 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	N Type Series
Body Length:	19.00mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Dielectric Withstanding Voltage:	>1500V
Durability:	>500 cycles
Flange Mount Length:	25.40mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710 & PEI
Max Operating Temperature:	+155°C
Min Operating Temperature:	-55°C
Mount Hole Distance:	18.30mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	18GHz
Pin Diameter:	1.27mm
Pin Length:	3.00mm
Ptfe Diameter:	6.00mm
Ptfe Length:	4.00mm
Thread Size:	5/8 24UNEF 2A
Voltage Max:	500V
Vswr:	<1.30

// Product PDF Links

[N Type Series Product Datasheet](#)