

Miniature cutting insert, type AK HW56 15

for internal recessing with radius

ATORN[®]



Application

For internal recessing with radius in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert with inner cooling

Advantage

- very hard cemented carbide type ensures low wear
- stable geometry for cutting insert
- extremely sharp cutting edges ensure cutting with process reliability

Art. no.	17130 252
ISO name	AK
Shaft diameter	6 mm
Length	51 mm
Clearance length	15 mm
Radius	0.75 mm
Recessing width	1.5 mm
Programming size 2	1.6 mm
Programming size	2.8 mm
Min. bore diameter	6.1 mm
Machining direction	Right
Carbide type	HW56 15
Material to be processed	Stainless steel, Non-ferrous metal

EAN-Code

4050293378863