

CUBE20S DIGITAL INPUT MODULE DI8

8x24VDC NPN

Expansion module
DI8 - (E) NPN

Link to Product**Illustration**

Product may differ from Image

Approvals**Input**

Sensor supply US	24 V DC (EN 61131-2), max. 500 mA per module
------------------	--

Type	NPN (EN 61131-2)
------	------------------

Input filter	3 ms
--------------	------

Galvanic isolation	500 V DC between inputs and internal communication
--------------------	--

Internal communication

Module Supply	via system connection
---------------	-----------------------

Current consumption	max. 60 mA
---------------------	------------

General data

Protection	IP20
------------	------

Connection	Spring clamp plug-in terminals: max. 1.5 mm ² (AWG 16)
------------	---

Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -20...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

Diagnostic

Communication status	via LED
Diagnostic via LED	per module and channel
Diagnostic via BUS	per module
Monitoring - under voltage	no
Monitoring - no voltage	yes
Short circuit and overload	yes

Commercial data

country of origin	TH
customs tariff number	85389099
minimum order quantity	1