

SRGC clamping holder, positive, right

For copy, longitudinal face lathing with RC indexable insert

ATORN[®]

Application

For longitudinal turning with RC indexable insert

Version

- Precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17850 514
ISO name	SRGC R/L 1616 H10
Shaft height	16 mm
Shank width	16 mm
Length	100 mm
Length of head	15.5 mm
Programming size	20 mm
Suitable for indexable inserts	RC.. 1003..
Tool design	Right

EAN-Code

4050293563115