

Collection tray for IBC containers

Steel, with grating

Application:

Prescribed storage of IBC containers and drums, for flammable liquids in GHS categories 1-3 and liquids which pose a hazard to water in GHS categories 1-4.

Execution:

- 3-mm thick welded sheet steel structure
- 100 mm ground clearance
- With galvanised grating (carrying capacity 1000 kg/m²)
- declaration of compliance (ÜHP) pursuant to StawaR



Art. no.	50060 290
Collection volume	1000 l
Max. number of 200-litre containers	10 PCS
Max. number of 1000-litre containers (IBC)	2 PCS
Length	2690 mm
Width	1650 mm
Height	375 mm
For liquids hazardous to water GHS 1-4	Yes
For flammable liquids GHS 1-3	Yes
Declaration of conformity in acc. with StawaR	Yes
With grating	Yes
With bottling attachment	No
Material	Sheet steel
Surface	Zinc plated
Gross Weight	294.000 kg
Product Group	5AI

EAN

4052462022669