

Flat-bed hand truck, 2-axle with towing eye

Open, carrying capacity 700 kg to 1250 kg

fetra
Transportgeräte

Execution:

- Modular system
- From welded profile steel, 4 tubular sleeves at corners
- Scissors-shaped drawbar with safety handle with soft rubber grip and with an automatic damped retraction in resting position
- Load area covered with slip-resistant phenolic resin coated waterproof plywood
- Wheels either with solid rubber or air tyres, hubs with roller bearings
- Automatic locking brake acting on the front wheels, according to EN 1757-3
- Drawbar eye, internal diameter 32 mm
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant



Art. no.	50267 860
Brand	FETRA
Manufacturer Part Number	6403VZ
Length	1545 mm
Height	1125 mm
Loading surface length	1200 mm
Width	800 mm
Loading-surface width	800 mm
Loading surface size	1200 x 800 mm
Loading-surface height	420 mm
Load-carrying capacity	700 kg
Total stop optional	No
Wheel width	60 mm
Wheel diameter	250 mm
Material of wheel	Solid rubber
Gross Weight	67.000 kg
Product Group	5AE

EAN

4017976214016

