

## Continental Device India Limited

An ISO/TS16949 and ISO 9001 Certified Company



2N2904 2N2905

TO-39 Metal Can Package

## PNP SILICON PLANAR SWITCHING TRANSISTORS



## **General Purpose Transistor**

### **ABSOLUTE MAXIMUM RATINGS**

DESCRIPTION	SYMBOL	VALUE	UNIT
Collector Emitter Voltage	$V_{CEO}$	40	V
Collector Base Voltage	$V_{CBO}$	60	V
Emitter Base Voltage	$V_{EBO}$	5	V
Collector Current Continuous	I <sub>C</sub>	600	mA
Power Dissipation @ T <sub>a</sub> =25°C	P <sub>D</sub>	600	mW
Derate Above 25°C		3.43	mW/ °C
Power Dissipation @ T <sub>c</sub> =25°C	$P_{D}$	3.0	W
Derate Above 25°C		17.2	mW/ °C
Operating And Storage Junction Temperature Range	$T_{j},T_{stg}$	- 65 to +200	°C

### ELECTRICAL CHARACTERISTICS (T<sub>a</sub>=25°C unless specified otherwise)

DESCRIPTION	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Collector Emitter Voltage	*V <sub>CEO</sub>	$I_C=10$ mA, $I_B=0$	40			V
Collector Base Voltage	$V_{CBO}$	$I_{C}=10\mu A, I_{E}=0$	60			V
Emitter Base Voltage	$V_{EBO}$	$I_E=10\mu A, I_C=0$	5			V
Collector Cut Off Current	I <sub>CEX</sub>	$V_{CE} = 30V, V_{BE} = 0.5V$			50	nA
Collector Cut Off Current	I <sub>CBO</sub>	$V_{CB}=50V$ , $I_{E}=0$			20	nA
		V <sub>CB</sub> =50V, I <sub>E</sub> =0, T <sub>a</sub> =150°C			20	μА
Base Current	I <sub>B</sub>	$V_{CE} = 30V, V_{BE} = 0.5V$			50	nA

			2N2904	2N2905	
DC Current Gain	h <sub>FE</sub>	I <sub>C</sub> =0.1mA, V <sub>CE</sub> =10V	>20	>35	
		$I_C=1$ mA, $V_{CE}=10$ V	>25	>50	
		$I_C=10$ mA, $V_{CE}=10$ V	>35	>75	
		*I <sub>C</sub> =150mA, V <sub>CE</sub> =10V	40 - 120	100 - 300	
		$^*I_C = 500 \text{mA}, V_{CE} = 10 \text{V}$	>20	>30	

\*Pulse Test: Pulse Width ≤ 300ms, Duty Cycle ≤ 2%



TO-39 Metal Can Package

## ELECTRICAL CHARACTERISTICS (T<sub>a</sub>=25°C unless specified otherwise)

#### **SMALL SIGNAL CHARACTERISTICS**

DESCRIPTION	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Collector Emitter Saturation Voltage	*V <sub>CE (sat)</sub>	$I_C=150$ mA, $I_B=15$ mA			0.4	V
		$I_C=500$ mA, $I_B=50$ mA			1.6	V
Base Emitter Saturation Voltage	*V <sub>BE (sat)</sub>	$I_C=150$ mA, $I_B=15$ mA			1.3	V
		$I_C=500$ mA, $I_B=50$ mA			2.6	V
Transition Frequency	**f <sub>T</sub>	I <sub>C</sub> =50mA, V <sub>CE</sub> =20V, f=100MHz	200			MHz
Output Capacitance	C <sub>obo</sub>	V <sub>CB</sub> =10V, I <sub>E</sub> =0, f=100KHz			8.0	pF
Input Capacitance	C <sub>ibo</sub>	$V_{BE}$ =2V, $I_{C}$ =0, f=100KHz			30	pF

#### **SWITCHING TIME**


DESCRIPTION	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Delay Time	$t_d$	I <sub>C</sub> =150mA, I <sub>B1</sub> =15mA,			10	ns
Rise Time	t <sub>r</sub>	$V_{CC}=30V$			40	ns
Turn On Time	ton	v.CC=20.v			45	ns
Storage Time	ţ	1 450m A 1			80	ns
Fall Time	t <sub>f</sub>	$I_{C}$ =150mA, $I_{B1}$ = $I_{B2}$ =15mA, $V_{CC}$ =6V			30	ns
Turn Off Time	t <sub>off</sub>	I <sub>B2</sub> =15IIIA, V <sub>CC</sub> =0V			100	ns

<sup>\*</sup>Pulse Test: Pulse Width < 300ms, Duty Cycle < 2%


 $<sup>^{**}</sup>$  f<sub>T</sub> is defined as the frequency at which  $\,$  Ih<sub>fe</sub>I extrapolates to unity.

## TO-39 Metal Can Package

# **TO-39 Metal Can Package**



DIM	MIN	MAX
Α	8.50	9.39
В	7.74	8.50
С	6.09	6.60
D	0.40	0.53
Ε	_	0.88
F	2.41	2.66
G	4.82	5.33
Н	0.71	0.86
J	0.73	1.02
Κ	12.70	_
L	42 DEG	48 DEG





All dimensions are in mm

PIN CONFIGURATION

- 1. EMITTER
- 2. BASE
- 3. COLLECTOR

# **Packing Detail**

PACKAGE	STANDARD PACK		INNER CARTON BOX		OUTER CARTON BOX		
	Details	Net Weight /Qty	Size	Qty	Size Oty Gr		Gr Wt
TO-39	500 pcs/polybag	540 gm/500 pcs	3" x 7.5" x 7.5"	20K	17" x 15" x 13.5"	32K	40 kgs

Notes 2N2904 2N2905

TO-39 Metal Can Package

#### **Disclaimer**

The product information and the selection guides facilitate selection of the CDIL's Discrete Semiconductor Device(s) best suited for application in your product(s) as per your requirement. It is recommended that you completely review our Data Sheet(s) so as to confirm that the Device(s) meet functionality parameters for your application. The information furnished in the Data Sheet and on the CDIL Web Site/CD are believed to be accurate and reliable. CDIL however, does not assume responsibility for inaccuracies or incomplete information. Furthermore, CDIL does not assume liability whatsoever, arising out of the application or use of any CDIL product; neither does it convey any license under its patent rights nor rights of others. These products are not designed for use in life saving/support appliances or systems. CDIL customers selling these products (either as individual Discrete Semiconductor Devices or incorporated in their end products), in any life saving/support appliances or systems or applications do so at their own risk and CDIL will not be responsible for any damages resulting from such sale(s).

CDIL strives for continuous improvement and reserves the right to change the specifications of its products without prior notice.



CDIL is a registered Trademark of
Continental Device India Limited
C-120 Naraina Industrial Area, New Delhi 110 028, India.
Telephone + 91-11-2579 6150, 5141 1112 Fax + 91-11-2579 5290, 5141 1119
emai@cdil.com, www.cdilsemi.com