



SITOR FUSE-LINK FOR SEMICONDUCTOR
PROTECTION 125A AR 2500V SIZE 3 CONNECTION
CONTACT INDICATOR 260MM

Figure similar

Model		
product brand name		SENTRON
Design of an identification indicator		front indicator
Design of the fuse link		Semiconductor protection fuse link
General technical data		
Size of fuse system / acc. to DIN EN 60269-1		NH3
Operating class of the fuse link		aR
circuit-breaker / Design		3NE
Switching capacity		
Switching capacity current		
• acc. to IEC 60947-2 / Rated value	kA	100
Electricity		
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	125
Current / with AC / Rated value	A	125
Mechanical Design		
mounting position		Any, preferably vertical
Environmental conditions		
Ambient temperature		
• minimum	°C	-20
• maximum	°C	50
Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		F

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NE96221C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NE96221C/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NE96221C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015