

# Mini guided actuator DFC-10-5-P-A-GF

Part number: 189467

FESTO



## Data sheet

Feature	Value
Distance of centre of gravity of payload to yoke plate xs	15 mm
Stroke	5 mm
Piston diameter	10 mm
Type code	DFC
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Sliding guide
Design	Guide
Position sensing	For proximity sensor
Symbol	00991737
Operating pressure	1 bar ... 10 bar
Max. speed	1 m/s
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-5 °C ... 60 °C
Impact energy in the end positions	0.05 J
Max. torque Mx	0.4 Nm
Max. payload as a function of the stroke at defined distance xs	12.2 N
Theoretical force at 6 bar, retracting	35 N
Theoretical force at 6 bar, advancing	47 N
Moving mass	8.8 g
Moving mass at 0 mm stroke	8.8 g
Product weight	91 g
Additional moving mass per 10 mm stroke	2.8 g
Pneumatic connection	M5
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel