

Platform scales DE-D



Application:

For versatile use in various locations such as production, warehousing and shipping.

Execution:

- Dual range scales with automatic switch-over
- Display unit (degree of protection IP65) with 1.5 m cable
- Options: Stand for display unit
- Freely-programmable weighing unit, e.g. displays in thread length g/m, paper weight g/m²
- Formulation function for weighing different components
- Backlit LCD display with 25 mm digit size

Advantage:

- Dual measurement display for finer digit increment and higher accuracy in the initial weighing range
- Versatile positioning of display unit, free-standing or bolted to scales

Delivery:

Mains adapter



Art. no.	44618 230
Brand	KERN
Manufacturer Part Number	DE 35K5D
Type description	DE 35K5D
Max. weight measuring range	15 kg
Max. weight measuring range 2	35 kg
Digit increment, weight	5 g
Digit increment 2, weight	10 g
Plate size	315 x 305 mm
With unit counting	Yes
Min. item weight	10 g
Reproducibility	5 g
Reproducibility 2	10 g
Linearity	15 g
Linearity 2	30 g
Data transmission type	RS232
Gross Weight	5.600 kg
Product Group	447

EAN

4045761123359