

EET-1056P-9 ✓ ACTIVE

TE Internal #: 2-1768018-5

Standard Labels, Blank Labels, Die-Cut Label Style, Permanent, UL Listed No, Label Width 56 mm [2.2 in], Label Height .374 in [9.5 mm], White

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels



Label Type: **Blank Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent**

UL Listed: **No**

Label Width: **56 mm [2.2 in]**

Features

Product Type Features

Label Type	Blank Labels
------------	--------------

Body Features

Label Color	White
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--

Recommended Printer Ribbon	See Printer Ribbon Matrix
----------------------------	---------------------------

Printer Technology	Thermal Transfer
--------------------	------------------

Label Style	Die-Cut
-------------	---------

Label Width	56 mm[2.2 in]
-------------	---------------

Label Height	9.5 mm[.374 in]
--------------	-----------------

Label Material	Polyester
----------------	-----------

Label Thickness	104 Micron
-----------------	------------

Industry Standards

UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	3000
--------------------	------



Packaging Method	Box
Other	
Label Adhesive Type	Permanent

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1768018-4
EET-0848P-9



TE Part # 3-1768018-5
EET-1113P-9

Customers Also Bought



Documents

Product Drawings

[EET-1056P-9](#)

English

Datasheets & Catalog Pages

[EET Technical Datasheet](#)

English