

- I/O isolation 5000 VAC (reinforced)
- Short circuit protection
- Semi-regulated outputs
- Input voltage ranges ( $\pm 10\%$ ):  
5, 12, 15, 24 VDC
- Operating temperature range  
-40 to +85 °C without derating
- Certification according to IEC/EN/ES  
60601-1 3rd edition for 2xMOPP and  
IEC/EN/UL 62368-1
- Low leakage current  $< 2 \mu\text{A}$
- Efficiency up to 85%
- Operation up to 5000 m altitude
- 5-year product warranty



ES 60601-1 IEC 60601-1  
UL 62368-1 IEC 62368-1

The TRV 1M is a series of 1 Watt DC/DC converters in a compact SIP-9 package with reinforced isolation of 5000 VAC for medical and industrial applications. The series offers models with different input voltages ( $\pm 10\%$ ) between 5 and 24 VDC. With a continuous short circuit protection and a low leakage current of less than  $2 \mu\text{A}$ , this converter series is especially suited to protect any connected interfaces or applied parts to patients. Featuring semi-regulated outputs this series provides a good level of regulation without affecting the cost efficiency. It is an ideal solution for applications where a completely unregulated DC/DC converter would not meet your regulation requirements and therefore opens up the overall application range of this series. Together with an operating temperature range from -40 to +85°C without derating and certifications according to IEC/EN/ES 60601-1 3rd ed. for 2xMOPP and IEC/EN/UL 62368-1 this series is suitable for many different applications where a medical isolation system and short circuit protection is needed.

### Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I <sub>max</sub>	Vnom	I <sub>max</sub>	
TRV 1-0510M	4.5 - 5.5 VDC (5 VDC nom.)	3.3 VDC	303 mA			80 %
TRV 1-0511M		5 VDC	200 mA			82 %
TRV 1-0512M		12 VDC	83 mA			85 %
TRV 1-0513M		15 VDC	67 mA			84 %
TRV 1-0521M		+5 VDC	100 mA	-5 VDC	100 mA	85 %
TRV 1-0522M		+12 VDC	42 mA	-12 VDC	42 mA	85 %
TRV 1-0523M		+15 VDC	34 mA	-15 VDC	34 mA	84 %
TRV 1-1210M	9.6 - 14.4 VDC (12 VDC nom.)	3.3 VDC	303 mA			80 %
TRV 1-1211M		5 VDC	200 mA			82 %
TRV 1-1212M		12 VDC	83 mA			84 %
TRV 1-1213M		15 VDC	67 mA			83 %
TRV 1-1221M		+5 VDC	100 mA	-5 VDC	100 mA	82 %
TRV 1-1222M		+12 VDC	42 mA	-12 VDC	42 mA	83 %
TRV 1-1223M		+15 VDC	34 mA	-15 VDC	34 mA	83 %
TRV 1-1510M	12 - 18 VDC (15 VDC nom.)	3.3 VDC	303 mA			79 %
TRV 1-1511M		5 VDC	200 mA			83 %
TRV 1-1512M		12 VDC	83 mA			84 %
TRV 1-1513M		15 VDC	67 mA			84 %
TRV 1-1521M		+5 VDC	100 mA	-5 VDC	100 mA	82 %
TRV 1-1522M		+12 VDC	42 mA	-12 VDC	42 mA	83 %
TRV 1-1523M		+15 VDC	34 mA	-15 VDC	34 mA	83 %
TRV 1-2410M	19.2 - 28.8 VDC (24 VDC nom.)	3.3 VDC	303 mA			78 %
TRV 1-2411M		5 VDC	200 mA			82 %
TRV 1-2412M		12 VDC	83 mA			83 %
TRV 1-2413M		15 VDC	67 mA			83 %
TRV 1-2421M		+5 VDC	100 mA	-5 VDC	100 mA	80 %
TRV 1-2422M		+12 VDC	42 mA	-12 VDC	42 mA	81 %
TRV 1-2423M		+15 VDC	34 mA	-15 VDC	34 mA	81 %

Note - 5 Vin models: If the input will be switched electromechanically, use an external 100  $\mu\text{F}/10 \text{ V E/C}$ . to avoid voltage transient.

### Input Specifications

Input Current	- At no load	5 Vin models: <b>30 mA typ.</b> 12 Vin models: <b>30 mA typ.</b> 15 Vin models: <b>15 mA typ.</b> 24 Vin models: <b>10 mA typ.</b>
Surge Voltage		5 Vin models: <b>6 VDC max.</b> (1 s max.) 12 Vin models: <b>25 VDC max.</b> (1 s max.) 15 Vin models: <b>25 VDC max.</b> (1 s max.) 24 Vin models: <b>40 VDC max.</b> (1 s max.)
Recommended Input Fuse		5 Vin models: <b>500 mA</b> (slow blow) 12 Vin models: <b>315 mA</b> (slow blow) 15 Vin models: <b>315 mA</b> (slow blow) 24 Vin models: <b>160 mA</b> (slow blow) (The need of an external fuse has to be assessed in the final application.)

### Output Specifications

Voltage Set Accuracy		<b>±3.5% max.</b> (60% load: 3.3, 5, ±5 Vout models) <b>±3.5% max.</b> (90% load: other models)
Regulation	- Input Variation (1% Vin step)  - Load Variation (10 - 100%)  - Cross Regulation (25% / 100% asym. load)	single output models: <b>0.2% max.</b> dual output models: <b>0.2% max.</b> single output models: <b>10% max.</b> (3.3, 5 Vout models) <b>7% max.</b> (other models) dual output models: <b>7% max.</b> (Output 1) <b>7% max.</b> (Output 2) (10% max. for ±5 Vout model) dual output models: <b>6% max.</b>
Ripple and Noise	- 20 MHz Bandwidth	<b>75 mVp-p typ.</b> <b>100 mVp-p max.</b>
Capacitive Load	- single output  - dual output	3.3 Vout models: <b>2'000 µF max.</b> 5 Vout models: <b>820 µF max.</b> 12 Vout models: <b>470 µF max.</b> 15 Vout models: <b>470 µF max.</b> 5 / -5 Vout models: <b>470 / 470 µF max.</b> 12 / -12 Vout models: <b>220 / 220 µF max.</b> 15 / -15 Vout models: <b>220 / 220 µF max.</b>
Minimum Load		Not required
Temperature Coefficient		<b>±0.03 %/K max.</b>
Short Circuit Protection		Continuous, Automatic recovery

### Safety Specifications

Safety Standards	- IT / Multimedia Equipment  - Medical Equipment  - Certification Documents	EN 62368-1 IEC 62368-1 UL 62368-1 EN 60601-1 IEC 60601-1 ANSI/AAMI ES 60601-1 2 x MOPP (Means Of Patient Protection) <a href="http://www.tracopower.com/overview/trv1m">www.tracopower.com/overview/trv1m</a>
------------------	---	--

All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

## EMC Specifications

<b>EMI Emissions</b>		EN 60601-1-2 edition 4 (Medical Devices)
- Conducted Emissions		EN 55011 class A (with external filter) EN 55011 class B (with external filter) EN 55032 class A (with external filter) EN 55032 class B (with external filter)
- Radiated Emissions		EN 55011 class A (with external filter) EN 55011 class B (with external filter) EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	External filter proposal:	<a href="http://www.tracopower.com/overview/trv1m">www.tracopower.com/overview/trv1m</a>
<b>EMS Immunity</b>		EN 60601-1-2 edition 4 (Medical Devices)
- Electrostatic Discharge	Air:	EN 61000-4-2, ±15 kV, perf. criteria A
	Contact:	EN 61000-4-2, ±8 kV, perf. criteria A
- RF Electromagnetic Field		EN 61000-4-3, 10 V/m, perf. criteria A
- EFT (Burst) / Surge		EN 61000-4-4, ±2 kV, perf. criteria A EN 61000-4-5, ±2 kV, perf. criteria A
	External filter proposal:	<a href="http://www.tracopower.com/overview/trv1m">www.tracopower.com/overview/trv1m</a>
- Conducted RF Disturbances		EN 61000-4-6, 10 Vrms, perf. criteria A
- PF Magnetic Field	Continuous:	EN 61000-4-8, 100 A/m, perf. criteria A
	1 s:	EN 61000-4-8, 1000 A/m, perf. criteria A

## General Specifications

<b>Relative Humidity</b>		95% max. (non condensing)
<b>Temperature Ranges</b>	- Operating Temperature	-40°C to +85°C (without derating)
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
<b>Cooling System</b>		Natural convection (20 LFM)
<b>Altitude During Operation</b>		5'000 m max.
<b>Switching Frequency</b>		220 - 380 kHz (PWM)
<b>Insulation System</b>		Reinforced Insulation
<b>Working Voltage (rated)</b>		250 VAC
<b>Isolation Test Voltage</b>	- Input to Output, 60 s	5'000 VAC
<b>Creepage</b>	- Input to Output	8 mm min.
<b>Clearance</b>	- Input to Output	8 mm min.
<b>Isolation Resistance</b>	- Input to Output, 500 VDC	10'000 MΩ min.
<b>Isolation Capacitance</b>	- Input to Output, 100 kHz, 1 V	15 pF typ. 20 pF max.
<b>Leakage Current</b>	- Touch Current	2 µA max.
<b>Reliability</b>	- Calculated MTBF	19'360'000 h (MIL-HDBK-217F, ground benign)
<b>Environment</b>	- Vibration	MIL-STD-810F
	- Mechanical Shock	MIL-STD-810F
	- Thermal Shock	MIL-STD-810F
<b>Housing Material</b>		Non-conductive Plastic (UL94 V-0 rated)
<b>Potting Material</b>		Silicone (UL 94 V-0 rated)
<b>Pin Material</b>		Brass
<b>Pin Foundation Plating</b>		Nickel (1 - 2 µm)
<b>Pin Surface Plating</b>		Tin (3 - 5 µm), matte
<b>Connection Type</b>		THD (Through-Hole Device)
<b>Weight</b>		4.8 g
<b>Environmental Compliance</b>	- REACH Declaration	<a href="http://www.tracopower.com/info/reach-declaration.pdf">www.tracopower.com/info/reach-declaration.pdf</a> REACH SVHC list compliant REACH Annex XVII compliant
	- RoHS Declaration	<a href="http://www.tracopower.com/info/rohs-declaration.pdf">www.tracopower.com/info/rohs-declaration.pdf</a> Exemptions: 7a, 7c-I


All specifications valid at nominal voltage, full load and +25°C after warm-up time unless otherwise stated.

### Supporting Documents

Overview Link (for additional Documents)

[www.tracopower.com/overview/trv1m](http://www.tracopower.com/overview/trv1m)

### Outline Dimensions



Dimensions in mm (inch)  
 Tolerances: x.x ±0.5 (±0.02)  
 x.xx ±0.25 (±0.01)  
 Pin diameter ±0.1 (±0.004)

### Pinout

Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
7	-Vout	-Vout
8	No Pin	Common
9	+Vout	+Vout