

## Horizontal quick-action clamp

With open clamping arm and angular base



### Application:


For quick and secure clamping on machine tables and appliances.

### Version:

- Galvanised and passivated
- With red oil-resistant plastic handle
- Case-hardened and lubricated bearing bushes
- Stainless steel rivet
- Ergonomic, oil-resistant handle with large hand rest and soft components
- Protection against the loss of the clamping screw on the end of the clamping arm

### Delivery:

With tempered and galvanised thrust bolt



<b>Art. no.</b>	<b>26216 020</b>
<b>Size</b>	2
<b>Hole distance</b>	20 mm
<b>Hole distance 2</b>	25.5 mm
<b>Bore diameter</b>	5.6 mm
<b>Clamping height</b>	73 mm
<b>Retaining force</b>	1000 N
<b>Max. tensile force</b>	1200 N
<b>Height</b>	94 mm
<b>Length</b>	162 mm
<b>Thumbscrew size</b>	M6 x 35 mm

### EAN-Code

4020772093327