LMC6084

LMC6084 Precision CMOS Quad Operational Amplifier



Literature Number: SNOS657C



LMC6084

Precision CMOS Quad Operational Amplifier

General Description

The LMC6084 is a precision quad low offset voltage operational amplifier, capable of single supply operation. Performance characteristics include ultra low input bias current, high voltage gain, rail-to-rail output swing, and an input common mode voltage range that includes ground. These features, plus its low offset voltage, make the LMC6084 ideally suited for precision circuit applications.

Other applications using the LMC6084 include precision full-wave rectifiers, integrators, references, and sample-and-hold circuits.

This device is built with National's advanced Double-Poly Silicon-Gate CMOS process.

For designs with more critical power demands, see the LMC6064 precision quad micropower operational amplifier.

For a single or dual operational amplifier with similar features, see the LMC6081 or LMC6082 respectively.

PATENT PENDING

Features


(Typical unless otherwise stated)

- Low offset voltage: 150 µV
- Operates from 4.5V to 15V single supply
- Ultra low input bias current: 10 fA
- Output swing to within 20 mV of supply rail, 100k load
- Input common-mode range includes V⁻
- High voltage gain: 130 dB
- Improved latchup immunity


Applications

- Instrumentation amplifier
- Photodiode and infrared detector preamplifier
- Transducer amplifiers
- Medical instrumentation
- D/A converter
- Charge amplifier for piezoelectric transducers

Connection Diagrams



Input Bias Current vs Temperature



Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Differential Input Voltage ±Supply Voltage Voltage at Input/Output Pin $(V^{+}) + 0.3V$, $(V^{-}) - 0.3V$ Supply Voltage (V+ - V-) 16V Output Short Circuit to V+ (Note 11)

Output Short Circuit to V-(Note 2)

Lead Temperature

(Soldering, 10 Sec.) 260°C

Storage Temp. Range -65°C to +150°C 150°C Junction Temperature

ESD Tolerance (Note 4) 2 kV Current at Input Pin ±10 mA Current at Output Pin ±30 mA 40 mA Current at Power Supply Pin Power Dissipation (Note 3)

Operating Ratings (Note 1)

Temperature Range

 $-55^{\circ}C \le T_{J} \le +125^{\circ}C$ LMC6084AM $-40^{\circ}\text{C} \le \text{T}_{\text{J}} \le +85^{\circ}\text{C}$ LMC6084AI, LMC6084I $4.5V \leq V^+ \leq 15.5V$ Supply Voltage

Thermal Resistance (θ_{JA}) (Note 12)

14-Pin Molded DIP 81°C/W 14-Pin SO 126°C/W Power Dissipation (Note 10)

DC Electrical Characteristics

Unless otherwise specified, all limits guaranteed for $T_J = 25^{\circ}\text{C}$. Boldface limits apply at the temperature extremes. $V^+ = 5V$, V^- = 0V, V_{CM} = 1.5V, V_{O} = 2.5V and R_{L} > 1M unless otherwise specified.

				Тур	LMC6084AM	LMC6084AI	LMC6084I	
Symbol	Parameter	Cond	itions	(Note 5)	Limit	Limit	Limit	Units
					(Note 6)	(Note 6)	(Note 6)	
Vos	Input Offset Voltage			150	350	350	800	μV
					1000	800	1300	Max
TCV _{os}	Input Offset Voltage			1.0				μV/°C
	Average Drift							
I _B	Input Bias Current			0.010				pА
					100	4	4	Max
I _{os}	Input Offset Current			0.005				pА
					100	2	2	Max
R _{IN}	Input Resistance			>10				Tera Ω
CMRR	Common Mode	0V ≤ V _{CM} ≤	12.0V	85	75	75	66	dB
	Rejection Ratio	V ⁺ = 15V			72	72	63	Min
+PSRR	Positive Power Supply	5V ≤ V ⁺ ≤ 1	ōV	85	75	75	66	dB
	Rejection Ratio	$V_{O} = 2.5V$			72	72	63	Min
-PSRR	Negative Power Supply	0V ≤ V ⁻ ≤ -	10V	94	84	84	74	dB
	Rejection Ratio				81	81	71	Min
V _{CM}	Input Common-Mode	V+ = 5V and	15V	-0.4	-0.1	-0.1	-0.1	V
	Voltage Range	for CMRR ≥ 60 dB			0	0	0	Max
				V ⁺ – 1.9	V ⁺ - 2.3	V ⁺ - 2.3	V ⁺ - 2.3	V
					V+ - 2.6	V ⁺ - 2.5	V ⁺ - 2.5	Min
A _V	Large Signal	$R_L = 2 k\Omega$	Sourcing	1400	400	400	300	V/mV
	Voltage Gain	(Note 7)			300	300	200	Min
			Sinking	350	180	180	90	V/mV
					70	100	60	Min
		$R_L = 600\Omega$	Sourcing	1200	400	400	200	V/mV
		(Note 7)			150	150	80	Min
			Sinking	150	100	100	70	V/mV
					35	50	35	Min

DC Electrical Characteristics (Continued)
Unless otherwise specified, all limits guaranteed for $T_J = 25^{\circ}C$. **Boldface** limits apply at the temperature extremes. $V^+ = 5V$, $V^- = 0V$, $V_{CM} = 1.5V$, $V_O = 2.5V$ and $R_L > 1M$ unless otherwise specified.

			Тур	LMC6084AM	LMC6084AI	LMC6084I	
Symbol	Parameter	Conditions	(Note 5)	Limit	Limit	Limit	Units
				(Note 6)	(Note 6)	(Note 6)	
Vo	Output Swing	V ⁺ = 5V	4.87	4.80	4.80	4.75	V
		$R_L = 2 k\Omega$ to 2.5V		4.70	4.73	mit Limit te 6) (Note 6) 80 4.75 73 4.67 13 0.20 17 0.24 50 4.40 31 4.21 40 0.50 50 0.63 .50 14.37 .34 14.25 35 0.44 45 0.56 .35 12.92 .86 12.44 16 1.33 32 1.58 6 13 10 8 6 13 10 8 23 23 12 18 28 23 18 23 18 23 18 23 18 23 18 23 19 18 20 3.0 3.6 3.6	Min
			0.10	0.13	0.13	0.20	V
				0.19	0.17	0.24	Max
		V+ = 5V	4.61	4.50	4.50	4.40	V
		$R_L = 600\Omega$ to 2.5V		4.24	4.31	4.21	Min
			0.30	0.40	0.40	0.50	V
				0.63	0.50	0.63	Max
		V ⁺ = 15V	14.63	14.50	14.50	14.37	V
		$R_L = 2 k\Omega$ to 7.5V		14.30	14.34	14.25	Min
			0.26	0.35	0.35	0.44	V
				0.48	0.45	0.56	Max
		V ⁺ = 15V	13.90	13.35	13.35	12.92	V
		$R_L = 600\Omega$ to 7.5V		12.80	12.86	12.44	Min
			0.79	1.16	1.16	1.33	V
				1.42	1.32	1.58	Max
lo	Output Current	Sourcing, V _O = 0V	22	16	0.17 4.50 4.31 0.40 0.50 14.50 14.34 0.35 0.45 13.35 12.86 1.16	13	mA
	V ⁺ = 5V			8	10	8	Min
		Sinking, V _O = 5V	21	16	16	13	mA
				11	13	10	Min
Io	Output Current	Sourcing, V _O = 0V	30	28	28	23	mA
	V ⁺ = 15V			18	1.16 1.32 16 10 16 13 28 22	18	Min
		Sinking, V _O = 13V	34	28	28	23	mA
		(Note 11)		19	(Note 6) 4.80 4.73 0.13 0.17 4.50 4.31 0.40 0.50 14.50 14.34 0.35 0.45 13.35 12.86 1.16 1.32 16 10 16 13 28 22 28 22 3.0 3.6	18	Min
Is	Supply Current	All Four Amplifiers	1.8	3.0	16 10 16 13 28 22 28 22 3.0	3.0	mA
		$V^+ = +5V, V_O = 1.5V$		3.6	3.6	3.6	Max
		All Four Amplifiers	2.2	3.4	3.4	3.4	mA
		$V^+ = +15V, V_O = 7.5V$		4.0	4.0	4.0	Max

AC Electrical Characteristics

Unless otherwise specified, all limits guaranteed for $T_J = 25^{\circ}C$, **Boldface** limits apply at the temperature extremes. $V^+ = 5V$, $V^- = 0V$, $V_{CM} = 1.5V$, $V_O = 2.5V$ and $R_L > 1M$ unless otherwise specified.

			Тур	LMC6084AM	LMC6084AI	LMC6084I	
Symbol	Parameter	Conditions	(Note 5)	Limit	Limit	Limit	Units
				(Note 6)	(Note 6)	(Note 6)	
SR	Slew Rate	(Note 8)	1.5	0.8	0.8	0.8	V/µs
				0.5	0.6	0.6	Min
GBW	Gain-Bandwidth Product		1.3				MHz
φ _m	Phase Margin		50				Deg
	Amp-to-Amp Isolation	(Note 9)	140				dB
e _n	Input-Referred Voltage Noise	F = 1 kHz	22				nV/√ Hz
i _n	Input-Referred Current Noise	F = 1 kHz	0.0002				pA/√ Hz
T.H.D.	Total Harmonic Distortion	$F = 10 \text{ kHz}, A_V = -10$					
		$R_L = 2 k\Omega, V_O = 8 V_{PP}$	0.01				%
		±5V Supply					

Note 1: Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but do not guarantee specific performance limits. For guaranteed specifications and test conditions, see the Electrical Characteristics. The guaranteed specifications apply only for the test conditions listed.

Note 2: Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Output currents in excess of ±30 mA over long term may adversely affect reliability.

Note 3: The maximum power dissipation is a function of $T_{J(Max)}$, θ_{JA} , and T_A . The maximum allowable power dissipation at any ambient temperature is $P_D = (T_{J(Max)} - T_A)/\theta_{JA}$.

Note 4: Human body model, 1.5 k Ω in series with 100 pF.

Note 5: Typical values represent the most likely parametric norm.

Note 6: All limits are guaranteed by testing or statistical analysis.

Note 7: $V^+ = 15V$, $V_{CM} = 7.5V$ and R_L connected to 7.5V. For Sourcing tests, $7.5V \le V_O \le 11.5V$. For Sinking tests, $2.5V \le V_O \le 7.5V$.

Note 8: V⁺ = 15V. Connected as Voltage Follower with 10V step input. Number specified is the slower of the positive and negative slew rates.

Note 9: Input referred V⁺ = 15V and R_L = 100 $k\Omega$ connected to 7.5V. Each amp excited in turm with 1 kHz to produce V_O = 12 V_{PP} .


Note 10: For operating at elevated temperatures the device must be derated based on the thermal resistance θ_{JA} with $P_D = (T_J - T_A)/\theta_{JA}$. All numbers apply for packages soldered directly into a PC board.

Note 11: Do not connect output to V+, when V+ is greater than 13V or reliability will be adversely affected.


 $\textbf{Note 12:} \ \ \textbf{All numbers apply for packages soldered directly into a PC board.}$

Typical Performance Characteristics


Distribution of LMC6084 Input Offset Voltage (T_A = +25°C)




Distribution of LMC6084 Input Offset Voltage (T_A = +125°C)




Supply Current vs Supply Voltage




Distribution of LMC6084 Input Offset Voltage (T_A = -55°C)



Input Bias Current vs Temperature




Input Voltage vs Output Voltage




Typical Performance Characteristics (Continued)







Power Supply Rejection Ratio vs Frequency




Input Voltage Noise vs Frequency




Output Characteristics Sourcing Current



Output Characteristics Sinking Current




Gain and Phase Response vs Temperature (-55°C to +125°C)




01146728

Typical Performance Characteristics (Continued)


Gain and Phase Response vs Capacitive Load with R_L = 600Ω



Open Loop Frequency Response




Inverting Large Signal Pulse Response




01146733

7

$\label{eq:Gain and Phase}$ Response vs Capacitive Load $\text{with R}_{\text{L}} = 500 \text{ k}\Omega$



Inverting Small Signal Pulse Response




TIME (1 μ s/Div)

01146732

01146730


Non-Inverting Small Signal Pulse Response




TIME (1 μ s/Div)

01146734

Typical Performance Characteristics (Continued)








AMPLIFIER TOPOLOGY


The LMC6084 incorporates a novel op-amp design topology that enables it to maintain rail-to-rail output swing even when driving a large load. Instead of relying on a push-pull unity gain output buffer stage, the output stage is taken directly from the internal integrator, which provides both low output impedance and large gain. Special feed-forward compensation design techniques are incorporated to maintain stability over a wider range of operating conditions than traditional micropower op-amps. These features make the LMC6084 both easier to design with, and provide higher speed than products typically found in this ultra-low power class.

COMPENSATING FOR INPUT CAPACITANCE

It is quite common to use large values of feedback resistance for amplifiers with ultra-low input current, like the LMC6084.

Although the LMC6084 is highly stable over a wide range of operating conditions, certain precautions must be met to achieve the desired pulse response when a large feedback resistor is used. Large feedback resistors and even small values of input capacitance, due to transducers, photodiodes, and circuit board parasitics, reduce phase margins.





When high input impedances are demanded, guarding of the LMC6084 is suggested. Guarding input lines will not only reduce leakage, but lowers stray input capacitance as well. (See *Printed-Circuit-Board Layout for High Impedance Work*)

The effect of input capacitance can be compensated for by adding a capacitor, $C_{\rm f}$, around the feedback resistors (as in *Figure 1*) such that:

$$\frac{1}{2\pi R_1 C_{IN}} \geq \frac{1}{2\pi R_2 C_f}$$

or
$$R_1 C_{IN} \le R_2 C_f$$

Since it is often difficult to know the exact value of $C_{\rm IN}$, $C_{\rm f}$ can be experimentally adjusted so that the desired pulse response is achieved. Refer to the LMC660 and LMC662 for a more detailed discussion on compensating for input capacitance.

Applications Hints (Continued)




FIGURE 1. Cancelling the Effect of Input Capacitance

CAPACITIVE LOAD TOLERANCE

All rail-to-rail output swing operational amplifiers have voltage gain in the output stage. A compensation capacitor is normally included in this integrator stage. The frequency location of the dominant pole is affected by the resistive load on the amplifier. Capacitive load driving capability can be optimized by using an appropriate resistive load in parallel with the capacitive load (see typical curves).

Direct capacitive loading will reduce the phase margin of many op-amps. A pole in the feedback loop is created by the combination of the op-amp's output impedance and the capacitive load. This pole induces phase lag at the unity-gain crossover frequency of the amplifier resulting in either an oscillatory or underdamped pulse response. With a few external components, op amps can easily indirectly drive capacitive loads, as shown in *Figure 2*.




FIGURE 2. LMC6084 Noninverting Gain of 10 Amplifier, Compensated to Handle Capacitive Loads

In the circuit of *Figure 2*, R1 and C1 serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving phase margin in the overall feedback loop.

Capacitive load driving capability is enhanced by using a pull up resistor to V $^+$ Figure 3. Typically a pull up resistor conducting 500 μ A or more will significantly improve capacitive load responses. The value of the pull up resistor must be determined based on the current sinking capability of the amplifier with respect to the desired output swing. Open loop gain of the amplifier can also be affected by the pull up resistor (see Electrical Characteristics).




FIGURE 3. Compensating for Large Capacitive Loads with a Pull Up Resistor

PRINTED-CIRCUIT-BOARD LAYOUT FOR HIGH-IMPEDANCE WORK

It is generally recognized that any circuit which must operate with less than 1000 pA of leakage current requires special layout of the PC board. When one wishes to take advantage of the ultra-low bias current of the LMC6084, typically less than 10 fA, it is essential to have an excellent layout. Fortunately, the techniques of obtaining low leakages are quite simple. First, the user must not ignore the surface leakage of the PC board, even though it may sometimes appear acceptably low, because under conditions of high humidity or dust or contamination, the surface leakage will be appreciable.

To minimize the effect of any surface leakage, lay out a ring of foil completely surrounding the LMC6084's inputs and the terminals of capacitors, diodes, conductors, resistors, relay terminals, etc. connected to the op-amp's inputs, as in Figure 4. To have a significant effect, guard rings should be placed on both the top and bottom of the PC board. This PC foil must then be connected to a voltage which is at the same voltage as the amplifier inputs, since no leakage current can flow between two points at the same potential. For example, a PC board trace-to-pad resistance of $10^{12}\Omega$, which is normally considered a very large resistance, could leak 5 pA if the trace were a 5V bus adjacent to the pad of the input. This would cause a 100 times degradation from the LMC6084's actual performance. However, if a guard ring is held within 5 mV of the inputs, then even a resistance of $10^{11}\Omega$ would cause only 0.05 pA of leakage current. See Figure 5 for typical connections of guard rings for standard op-amp configurations.

Applications Hints (Continued)






FIGURE 4. Example of Guard Ring in P.C. Board Layout



Inverting Amplifier







FIGURE 5. Typical Connections of Guard Rings

The designer should be aware that when it is inappropriate to lay out a PC board for the sake of just a few circuits, there

is another technique which is even better than a guard ring on a PC board: Don't insert the amplifier's input pin into the board at all, but bend it up in the air and use only air as an insulator. Air is an excellent insulator. In this case you may have to forego some of the advantages of PC board construction, but the advantages are sometimes well worth the effort of using point-to-point up-in-the-air wiring. See *Figure*

Latchup

CMOS devices tend to be susceptible to latchup due to their internal parasitic SCR effects. The (I/O) input and output pins look similar to the gate of the SCR. There is a minimum current required to trigger the SCR gate lead. The LMC6084 is designed to withstand 100 mA surge current on the I/O pins. Some resistive method should be used to isolate any capacitance from supplying excess current to the I/O pins. In addition, like an SCR, there is a minimum holding current for any latchup mode. Limiting current to the supply pins will also inhibit latchup susceptibility.



0114671

(Input pins are lifted out of PC board and soldered directly to components. All other pins connected to PC board).

FIGURE 6. Air Wiring


Typical Single-Supply Applications

 $(V^+ = 5.0 V_{DC})$

The extremely high input impedance, and low power consumption, of the LMC6084 make it ideal for applications that require battery-powered instrumentation amplifiers. Examples of these types of applications are hand-held pH probes, analytic medical instruments, magnetic field detectors, gas detectors, and silicon based pressure transducers. Figure 7 shows an instrumentation amplifier that features high differential and common mode input resistance (>10¹⁴ Ω), 0.01% gain accuracy at $A_V = 1000$, excellent CMRR with 1 k Ω imbalance in bridge source resistance. Input current is less than 100 fA and offset drift is less than

CMRR with 1 k Ω imbalance in bridge source resistance. Input current is less than 100 fA and offset drift is less than 2.5 μ V/°C. R₂ provides a simple means of adjusting gain over a wide range without degrading CMRR. R₇ is an initial trim used to maximize CMRR without using super precision matched resistors. For good CMRR over temperature, low drift resistors should be used.

Typical Single-Supply Applications (Continued)



If $R_1 = R_5$, $R_3 = R_6$, and $R_4 = R_7$; then

$$\frac{v_{OUT}}{v_{IN}} = \frac{R_2 \, + \, 2\,R_1}{R_2} \times \frac{R_4}{R_3}$$

 $\therefore A_V \approx 100$ for circuit shown (R₂ = 9.822k).

FIGURE 7. Instrumentation Amplifier




FIGURE 8. Low-Leakage Sample and Hold

Typical Single-Supply Applications (Continued)





FIGURE 9. 1 Hz Square Wave Oscillator


Ordering Information

Package	Tempe	NSC	Transport	
	Military Industrial		Drawing	Media
	–55°C to +125°C	-40°C to +85°C		
14-Pin		LMC6084AIN	N14A	Rail
Molded DIP		LMC6084IN		
14-Pin		LMC6084AIM, LMC6084AIMX	M14A	Rail
Small Outline		LMC6084IM, LMC6084IMX		Tape and Reel


For MIL-STD-883C qualified products, please contact your local National Semiconductor Sales Office or Distributor for availability and specification information.

Physical Dimensions inches (millimeters) unless otherwise noted





14-Pin Small Outline Package (M)
Order Number LMC6084AIM, LMC6084IMX, LMC6084IM or LMC6084IMX
NS Package Number M14A



14-Pin Molded Dual-In-Line Package (N)
Order Number LMC6084AIN or LMC6084IN
NS Package Number N14A

Notes

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

For the most current product information visit us at www.national.com.

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

BANNED SUBSTANCE COMPLIANCE

National Semiconductor certifies that the products and packing materials meet the provisions of the Customer Products Stewardship Specification (CSP-9-111C2) and the Banned Substances and Materials of Interest Specification (CSP-9-111S2) and contain no "Banned Substances" as defined in CSP-9-111S2.



National Semiconductor Americas Customer Support Center Email: new.feedback@nsc.com

Tel: 1-800-272-9959

www.national.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86

Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 69 9508 6208
English Tel: +44 (0) 870 24 0 2171
Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com National Semiconductor Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products Applications

Audio www.ti.com/audio Communications and Telecom www.ti.com/communications **Amplifiers** amplifier.ti.com Computers and Peripherals www.ti.com/computers dataconverter.ti.com Consumer Electronics www.ti.com/consumer-apps **Data Converters DLP® Products** www.dlp.com **Energy and Lighting** www.ti.com/energy DSP dsp.ti.com Industrial www.ti.com/industrial Clocks and Timers www.ti.com/clocks Medical www.ti.com/medical

Interface interface.ti.com Security www.ti.com/security

Logic Space, Avionics and Defense www.ti.com/space-avionics-defense

Power Mgmt power.ti.com Transportation and Automotive www.ti.com/automotive
Microcontrollers Microcontroller.ti.com Video and Imaging www.ti.com/video

RFID <u>www.ti-rfid.com</u>

OMAP Mobile Processors www.ti.com/omap

Wireless Connectivity www.ti.com/wirelessconnectivity

TI E2E Community Home Page <u>e2e.ti.com</u>