


DF2220



Circuit protection module for an uninterrupted power supply

Fuse/IO-Link/24VDC/2x1-10A



- 1 panel for labelling
- 2 pushbutton on / off / reset status LED 2
- 3 pushbutton on / off / reset status LED 1
- 4 push-in terminals Outputs 1/2



Application

Installation	rail TH35; according to EN 60715
--------------	----------------------------------

Electrical data

Operating voltage	[V]	to SELV/PELV
Nominal voltage DC	[V]	24
Input voltage DC	[V]	19,2...30
Protection class		III
Reverse polarity protection		yes
Mains buffering time (nominal voltage 24 V DC)	[ms]	10
Closed-circuit current	[mA]	12
Number of channels		2
Nominal current (Fail Safe Element)	[A]	10

Outputs

Load capacitance, total	[mF]	20
-------------------------	------	----

Operating conditions

Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...70
Protection		IP 20; (on the front)
Degree of soiling		2

Tests / approvals

EMC	EN 61000-6-3	radiation of interference
	EN 61000-6-2	immunity

DF2220



Circuit protection module for an uninterrupted power supply

Fuse/IO-Link/24VDC/2x1-10A

Mechanical data

Weight	[g]	74.4
Dimensions	[mm]	80 x 12.5 x 98

Displays / operating elements


Display	status	2 x LED, red / green / orange
Operating elements	2 x	pushbutton

Electrical connection

push-in terminals:


contact lever/strip:

Connection



Diagrams and graphs

output characteristics



time-current characteristics