



Features

- Dissipative
- Elastic
- Breathable
- Dust Free


Specifications

Colour : White Liner / White Fingertip Coating
 Material : 100% Pure Nylon (280 Denier with 13 Gauge)
 PU (Polyurethane) Fingertip Coating

Specification Table

Details	Tolerance	Small	Medium	Large	Extra Large
Length	±5mm	210mm	220mm	230mm	240mm
Palm Width	±3mm	85mm	85mm	87mm	87mm
Weight per glove	±1g	17mm	17.5mm	19mm	19.5mm
Wrist Colour	-	White	Green	Grey	Yellow

Cuff Colour



Palm Detail



Test Results

Technical Properties	Test Standard	Results
Surface Resistivity	-	$1 \times 10^{6-8} \Omega/\text{cm}$

Part Number Table

Description	Part Number
ESD PU Tip Glove, Medium, PK10	109-0917
ESD PU Tip Glove, Large, PK10	109-0918
ESD PU Tip Glove, Extra Large, PK10	109-0919

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.