

Lamellenstecker

Ø 2mm – Ø 2,5mm


Multilam™ plugs

Ø 2mm – Ø 2,5mm

Fiches à lamelles

Ø 2mm – Ø 2,5mm

Typ Type Type	Bestell-Nr. Order No. No. de Cde	Nenn-Ø Nominal-Ø Ø nominal	Anschlussvariante Type of termination Type de raccordement	Metallteile / Oberfläche Metal parts / plating Partie métallique / traitement	Auszugskraft Withdrawal force Effort de débrochage	Oberer Grenztemperatur Max. Temperature Température max.	Bemessungsstrom ¹⁾ Rated current ¹⁾ Intensité assignée ¹⁾	Kontaktwiderstand Contact resistance Résistance de contact
		mm			N	°C	A	mΩ




SA200	22.1100	2	M2	CuZn, Au	~4	150	25	0,4
-------	---------	---	----	----------	----	-----	----	-----

SA200N	22.1102	2	M2	CuZn, Ni	~4	150	25	2
--------	---------	---	----	----------	----	-----	----	---


Montagematerial bitte separat bestellen, siehe Seite 14.

Assembly material, please order separately, see page 14.


Accessoires de montage à commander séparément, voir page 14.



SA203	22.6303	2	Löten Soldering Souder	CuZn, Ni	~4	150	25	2
-------	---------	---	------------------------------	----------	----	-----	----	---



SA2,5	22.5118	2,5		CuZn, Au	~6	150	25	0,5
-------	---------	-----	--	----------	----	-----	----	-----



SA2,5-G	22.5117	2,5	M2,5	CuZn, Au	~6	150	25	0,5
---------	---------	-----	------	----------	----	-----	----	-----

¹⁾ je nach Anschlussart und Querschnitt

¹⁾ According to connecting method and cross section

¹⁾ Selon la méthode de raccordement et la section du conducteur