



IWLAN RCOAX N-CONNECT/SMA FEMALE/ FEMALE PANEL FEEDTHROUGH 2.4 GHZ AND 5 GHZ CABINET CABLE DUCT FOR MAXIMAL WALL THICKNESS 5.5 MM

Electrical data	
Number of electrical connections	2
Type of electrical connection	N-Connect female/SMA female
Transmission frequency	0 ... 6 GHz
Impedance	50 Ω
Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +70 °C
<ul style="list-style-type: none"> during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> during transport 	-40 ... +70 °C
Design, dimensions and weight	
Width	25.4 mm
Height	25.4 mm
Length	31.3 mm
Net weight	35 g
Standards, specifications, approvals	
Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
Further Information / Internet Links	
Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015