# swissbit<sup>®</sup>

**Product Fact Sheet** 

Industrial **CFexpress Card** 

**G-26 Series** CFexpress v2.0, Type B, 3D pSLC

#### Industrial Temperature Grade

Date: November 18, 2021 Revision: 1.00



Made in Germany

## Product Fact Sheet G-26 Series



## **Product Summary**

- Capacities: 5 GBytes, 10 GBytes, 20 GBytes, 40 GBytes, 80 GBytes, 160 GBytes
- Form Factor: CFexpress® Type B card (38.5mm x 29.6mm x 3.8mm)
- **Compliance**<sup>1</sup>: CFexpress v2.00
- Interface: PCIe Gen3 x 2 Lanes
- Command Sets: Supports NVMe 1.3
- Performance:
  - $\circ$  Read Performance: Sequential Read up to 1,620 MBytes/s, Random Read 4K up to 128,000 IOPS
  - Write Performance: Sequential Write up to 700 MBytes/s, Random Write 4K up to 121,000 IOPS
- Host Memory Buffer (HMB): Support for increased random performance
- Operating Temperature Range<sup>2</sup>:
  - Industrial: -40 °C to 85 °C
- Storage Temperature Range: -40°C to 85°C
- Operating Voltage: 3.3V supply voltage
- Low Power Consumption
- Power:
  - Power States PSo, PS1, PS2, PS3 and PS4
  - o Thermal Throttling supported
- Data Retention: 10 Years @ Life Begin; 1 Year @ Life End
  - High-Performance Processor with Integrated, Parallel Flash Interface Engines:
    - o 3D NAND Flash
    - LDPC Code ECC (up to 120bit corrections per 1KByte page)
- High Reliability
  - $\circ$   $\;$  Designed for Industrial and Automotive market
  - $\circ$  Ideal for applications like automation, embedded computing, gaming, IIoT and NetCom
  - $\circ$  Optimized for long life cycle that requires superior data retention as well as power fail safety
  - Mean Time Between Failure: >2,000,000 hours
  - Data Reliability: < 1 non-recoverable error per 10<sup>16</sup> bits read
  - Number of insertion/removal cycles: up to 12,000

<sup>&</sup>lt;sup>1</sup> The verification of host system and storage device compatibility is in customer's responsibility. Swissbit can provide guidance and support on request.

<sup>&</sup>lt;sup>2</sup> Adequate airflow is required to ensure the drive temperature, as reported in the S.M.A.R.T. data, does not exceed the specified maximum operating temperature.

## Product Fact Sheet G-26 Series



#### **Product Features**

- Dynamic and Static Wear Leveling
- Subpage Mode Flash Translation Layer (FTL)
- Data Care Management
  - Active: Adaptive Read Refresh
  - Passive: Background Media Scan
- Lifetime Enhancements
  - Dynamic Bad Block Remapping
  - $\circ$  Write Amplification Reduction
- Power Fail Data Loss Protection
- Data set management support (TRIM)
- Active State Power Management (ASPM) Support
- In-Field Firmware Update<sup>3</sup>
- Enterprise-Grade Self-Monitoring, Analysis, and Reporting Technology (S.M.A.R.T.)
- Gold-Plated Connector (IPC-6012B Class 2 Compliant)
- End-to-End (E2E) Data Protection
- AES256 Encryption (on request)
- Life Cycle Management, Controlled "Locked" BOM
- RoHS / REACH compliant
- Swissbit Life Time Monitoring (SBLTM) Tool and SDK for SBLTM (on request)



#### Order Information for G-26

| Density | Part Number                  | Temp. Range   | Flash Technology          |
|---------|------------------------------|---------------|---------------------------|
| 5GB     | SFCE005GW1EC1T0-I-5E-111-STD | -40°C to 85°C | 3D NAND Flash<br>SLC-mode |
| 10GB    | SFCE010GW1EC1T0-I-5E-111-STD |               |                           |
| 20GB    | SFCE020GW1EC2T0-I-5E-111-STD |               |                           |
| 40GB    | SFCE040GW1EC4T0-I-5E-111-STD |               |                           |
| 80GB    | SFCE080GW1EC4T0-I-6F-111-STD |               |                           |
| 160GB   | SFCE160GW1EC4WD-I-6F-111-STD |               |                           |

#### Why Swissbit?

Swissbit is focused on the design, development, manufacture, and support of leading edge memory and storage solutions for the worldwide OEM/ODM marketplace. As a global supplier, Swissbit recognizes and addressees the higher level of application requirements of today's industrial, Netcom, and automotive customers by providing best-in-class products and services, with uncsompromised attention to driving overall value and quality.

<sup>3</sup> The support of In-Field FW update capabilities on host systems is recommended.
Swissbit AG
Industriestrasse 4
TLP: Swissbit public

Industriestrasse 4 CH-9552 Bronschhofen Switzerland

www.swissbit.com/contact