

PSNN clamp holder, neutral

For chamfering and longitudinal turning using SN indexable insert

ATORN[®]

Application


For chamfering and longitudinal turning using SN indexable insert 90°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type S, 90° pitch angle, 90° tip angle, 0° clearance angle

Advantage

- extremely stable geometry for longitudinal machining with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths



Art. No.	17857 015
ISO name	PSDN N 3232 P12
Shaft height	32 mm
Shank width	32 mm
Length	170 mm
Length of head	28 mm
Programming size	16 mm
Suitable for indexable inserts	SN.. 1204..
Tool design	Neutral
DIN	4983

EAN-Code

405029334836 1