

Micrometer

With V-anvil

Mitutoyo

Application:

For measuring cutting tools, e.g. screw taps, cutters, reamers.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Friction coupling for consistent, repeatable measuring force
- Prism angle 60°

Delivery:

Includes box, setting standard, adjustment wrench



| | |
|---|---------------------|
| Art. no. | 32016 459 |
| Brand | MITUTOYO |
| Manufacturer Part Number | 114-204 |
| Min./max. length measuring range | 2.3-25 mm |
| Vernier scale | 0.01 mm |
| Measuring surface diameter | 6.3 mm |
| Measuring spindle increments | 0.5 mm |
| Opening angle | 60 Degree |
| Spindle clamping | Yes |
| Error limit | 4 µm |
| Display | Nonius |
| Type | three-flute V-anvil |
| Calibration Group | D, E |
| Gross Weight | 0.400 kg |
| Product Group | 3MA |

EAN

4946368010380