

Short taper-flange

Made of cast iron



Application:

For retroactive fastening of lathe chucks.

Execution:

- Ready-machined on machine side and chuck side, spindle heads with camlock fastening in accordance with DIN ISO 702-2 (formerly DIN 55029).

Art. no.	22510 101
Brand	BISON
Manufacturer Part Number	358245232100
Flange diameter	160 mm
Taper shank size	5
Pitch circle diameter	108 mm
Taper diameter	82.575 mm
Drill hole	79.5 mm
Ratio	95 mm
Number of bolts	4/6 pieces
Flange thickness	30 mm
Thread dimension	M8 x 6
Gross Weight	3.266 kg
Product Group	221

