

Shrink-fit chuck, 3 degrees

Long, slim design

ATORN[®]

Application

For clamping cutters and drills with straight shanks in h6 tolerance. Suitable for heavy-duty machining and all high-power applications. Suitable for inductive, contact and hot air shrinking devices.



Version

- guaranteed maximum concentricity 0.003 mm
- shrink grip and shrink release of HM and HSS tools
- hardness 52 + 2 HRC
- maximum coolant pressure 80 bar
- Glass bead blasted

Advantage

- Slimline design, extremely low interference contour
- High transmittable torques
- High positioning and repeat accuracy
- Ideal for high rotation speeds

Art. no.	23427 344
Clamping diameter	4 mm
Tapered diameter	10 mm
Outer diameter	17 mm
Projecting length	120 mm
Balancing quality	G 2.5 at 25 rpm

EAN-Code

4050293440195