



Part no.: 50030433
TKS 30X60
Reflector

Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50030433 – TKS 30X60 – Reflector

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	30 mm
Reflection surface width	27 mm
Mounting dimension, height	81 mm
Reflection surface height	56 mm
Mounting dimension, thickness	8.7 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	14 g
Type of fastening	Adhesive Through-hole mounting

Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

