

Enameled copper wire
CUL 100/0,50



Picture shows CUL 100/0,22

Advantages

Insulating varnish basis min, polyurethane, mod.

Grade 1, TJ min. 302 °F / 155 °C

Solderable

Applications

Enameled copper wire for the production of coils and windings and for general laboratory needs. Please consider the relevant standards.

Approvals



Enameled copper wire **CUL 100/0,50**

Type

CUL 100/0,50

Type

CUL 100/0,50



Electrical data



Mechanical data

Operating data

Current rating 0.7 A

Environment

Heat resistance 311 °F (CLF)

Insulating varnish min. Polyurethan, mod.

Tin-plate >662 °F

Measures and weights

Length m (min.) 44

Wire diameter 0.020 inch

Weight 0.22 lbs

Subject to change.