# TYPE EXAMINATION CERTIFICATE



Equipment or Protective System intended for use in Potentially Explosive Atmospheres
Directive 94/9/EC

- [3] Type Examination Certificate Number: **DEMKO 03 ATEX 135419X Rev. 1**
- [4] Equipment: Programmable Controllers, type AB75, AB76, AB78 or AB79 followed by 0-99
- [5] Manufacturer: HMS Industrial Networks AB

[2]

- [6] Address: Stationsgatan 37, 302 45 Halmstad, Sweden
- This equipment and any acceptable variation thereto are specified in the schedule to this certificate and the documents therein referred to.
- [8] UL International Demko A/S certifies that this equipment has been found to comply with the Essential Health and Safety Requirements that relate to the design of **Category 3** equipment, which is intended for use in potentially explosive atmospheres. These Essential Health and Safety Requirements are given in Annex II to the European Union Directive 94/9/EC of 23 March 1994.

The examination and test results are recorded in confidential report no. 4786797536

[9] Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the schedule of this certificate, has been assessed by reference to Standards:

EN 60079-0:2012+A11:2013 EN 60079-15:2010

- [10] If the sign "X" is placed after the certificate number, it indicates that the equipment or protective system is subject to special conditions for safe use specified in the schedule to this certificate.
- [11] This Type examination certificate relates only to the design of the specified equipment, and not to specific items of equipment subsequently manufactured.
- [12] The marking of the equipment or protective system shall include the following:



# Certification Manager

Jan-Erik Storgaard

This is to certify that the sample(s) of the Equipment described herein ("Certified Equipment") has been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the ATEX Equipment Certification Program Requirements. This certificate and test results obtained apply only to the equipment sample(s) submitted by the Manufacturer. UL did not select the sample(s) or determine whether the sample(s) provided were representative of other manufactured equipment. UL has not established Follow-Up Service or other surveillance of the equipment. The Manufacturer is solely and fully responsible for conformity of all equipment to all applicable Standards, specifications, requirements or Directives. The test results may not be used, in whole or in part, in any other document without UL's prior written approval.

**Date of issue:** 2004-05-28 **Re-issued:** 2015-10-27



**Certification Body** 

UL International Demko A/S, Borupvang 5A, 2750 Ballerup, Denmark Tel. +45 44 85 65 65, info.dk@ul.com, www.ul.com

[13]

[14]

# Schedule TYPE EXAMINATION CERTIFICATE No.

DEMKO 03 ATEX 165419X Rev. 1 Report: 4786797536

[15] <u>Description of Equipment:</u>

These devices are open type programmable controllers, type AB75, AB76, AB78 or AB79 followed by 0-99 and any or no suffix may follow depending on configuration/version (numbers or letters) for use in industrial automation applications in hazardous locations. They are microprocessor-based and communicate via interfaces through wire, to be supplied by a limited power source. The controllers have LED status indicators for both active and fault conditions. The overall housing is made of a metal housing or a metal housing with plastic top and bottom covers, for din DIN-rail mounting. The optical radiation output of the apparatus with respect to explosion protection, according to Annex II clause 1.3.1 of the Directive 94/9/EC is covered in this certificate.

The optical radiation output of the apparatus with respect to explosion protection, according to Annex II clause 1.3.1 of the Directive 94/9/EC is covered in this certificate

Nomenclature for type AB7acbd: abc-d (example: AB7566-B) or AB7bc-d

a) Article

AB7 Anybus Gateway

b) Module type

5, 6, 8, 9 Anybus X-gateway series

c) Product configuration

xx Individual product configuration based on option board and software etc. (numeric range from 00 – 99)

d) Configuration version

x Any or no suffix may follow depending on configuration/version (numbers or letters)

#### Temperature range

The relation between ambient temperature and the assigned temperature class is as follows:

Ambient temperature range -25 °C to +65 °C Temperature class

T4

24 Vdc ± 20%, 400mA

Electrical data:

Installation instructions

The programmable controllers shall be assembled in accordance with the instructions given by the manufacturer. Please refer to Description and Operating Instructions.

Routine tests:

No routine tests

### [16] <u>Descriptive Documents</u>

The scheduled drawings are listed in the report no. provided under item no. [8] on page 1 of this Type Examination Certificate.

## [17] Special conditions for safe use:

- Shall be used in an area with a classification of no more than pollution degree 2 and conforming to EN 60664-1, and in an enclosure with a tool removable cover, that complies with the relevant requirements of EN 60079-15, rated at least IP54.
- The device shall be connected to supply circuits where the rated voltage cannot be exceeded by 140% caused by transient disturbances.

## [18] <u>Essential Health and Safety Requirements</u>

Met by compliance with the standards EN 60079-0:2012+A11:2013 and EN 60079-15:2010.