


Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

**Product characteristics**

Frequency range	[Hz]	0...12000
-----------------	------	-----------

Application

Design	parameter setting via PC software VES004
--------	--

Electrical data

Operating voltage tolerance	[%]	20
-----------------------------	-----	----

Operating voltage	[V]	24 DC
-------------------	-----	-------

Current consumption	[mA]	200; ((24 V DC))
---------------------	------	------------------

Protection class	III
------------------	-----

Inputs / outputs

Total number of inputs and outputs	8; (configurable)
------------------------------------	-------------------

Number of inputs and outputs	Number of analogue inputs: 2; Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Inputs		
Total number of inputs		6
Number of analogue inputs		2; (static)
Analogue input (current) [mA]		0...20
Resolution of analogue input		12
Dynamic input - signal		0...10 mA IPE / 0...20 mA
Dynamic input - resolution [bit]		16
Dynamic input - frequency range [Hz]		0...12000
Dynamic input - sampling rate [kSamples]		100
Outputs		
Total number of outputs		2
Electrical design		PNP
Number of digital outputs		2; (configurable)
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]		2
Permanent current rating of switching output DC [mA]		100
Number of analogue outputs		1; (configurable)
Analogue current output [mA]		0...22
Max. load [Ω]		500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Frequency range [Hz]		0...12000
Interfaces		
Communication interface		Ethernet
Protocol		Modbus TCP
Operating conditions		
Ambient temperature [°C]		0...60
Storage temperature [°C]		0...60
Protection		IP 20
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV contact discharge / 15 kV air discharge
	EN 61000-4-3	10 V/m (80...2700 MHz)
	EN 61000-4-4 Burst	4 kV capacitive coupling probe, earthed
	EN 61000-4-6	10 V, 0,15...80 MHz
	EN 61000-6-4	industrial environments
	EN 50178	
MTTF [years]		91
UL approval	UL Approval no.	L001

Mechanical data		
Weight	[g]	304.5
Housing		plastic housing
Type of mounting		rail; (TH35/EN60715)
Dimensions	[mm]	114.2 x 50 x 105.3
Materials		PA
Data memories		
With real-time clock		yes
Real-time clock		yes;
Accessories		
Accessories (optional)		cross-over Ethernet patch cable for the direct connection to the PC
Remarks		
Pack quantity		1 pcs.
Electrical connection		
COMBICON:		
Connection		

