



Fxx*1) POGy*2)

e.g. F09P0G1

*1) xx No. of contacts 09, 15, 25 or 37
 *2) y for performance classes 1, 2 or 3
 (contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.9	25
15	39.1	25.2	33.3
25	53	38.9	47.04
37	69.3	55.3	63.5

② RoHS compliant

3	xx	Signal contact	P0 / Brass	AWG 20 / G1/G2/G3
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +125°C)	white
No.	St.	Part	Type Description/Material Surface plating/Colour/Class	

Measurement without tolerance occ. to		SCALE	TITLE
ISO 2768-m		2:1	
NAME / DATE	Denzinger		
	14-10-2002		
DRAWN	ffilmann		
CHECKED	24-08-2006		
2	24-08-2006	21889	
1			
REV.	DATE	CH.-NO.	DWG.NO.
			FxxP0Gy
			D-Sub Miniature Connector
			REPLACEMENT FOR:
			PAGES 1

