

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0643231029**  
**Status:** **Active**  
**Overview:** CMC and CMX Sealed, Hybrid, Modular Connectors  
**Description:** 1.50mm CMC CP Female Terminal, Tin Plated, for tab dimensions 1.5mm x 0.8mm, Wire Size 0.50mm<sup>2</sup> - 1.0mm<sup>2</sup>

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-64323-001-CH-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-64323-001-FR-001 (PDF)</a>
<a href="#">Product Specification PS-64319-002-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-CH-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-CH-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-FR-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-FR-001 (PDF)</a>	<a href="#">Application Specification AS-98420-001-SP-001 (PDF)</a>
<a href="#">Application Specification AS-64318-002-SP-001 (PDF)</a>	<a href="#">Application Specification AS-98420-002-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-001 (PDF)</a>	<a href="#">Application Specification AS-98420-002-CH-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-CH-001 (PDF)</a>	<a href="#">Application Specification AS-98420-002-FR-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-FR-001 (PDF)</a>	<a href="#">Application Specification AS-98420-002-SP-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-SP-001 (PDF)</a>	<a href="#">Packaging Specification PK-98915-001-001 (PDF)</a>
<a href="#">Application Specification AS-64323-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family Crimp Terminals  
 Series **64323**  
 Application Power, Wire-to-Wire  
 Comments \* Current tested on a fully loaded connector, current for temperature increase of 40°C. Current max = 12A for 1.50mm Terminal (2.00mm<sup>2</sup> wire)\*

Crimp Quality Equipment  
 Overview  
 Product Name  
 UPC


Yes  
[CMC and CMX Sealed, Hybrid, Modular Connectors](#)  
 CMC, CP Terminal  
 883906129583

**Physical**

Gender Female  
 Material - Metal High Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.340/g  
 Packaging Type Reel  
 Plating min - Mating 1.524µm, 3.048µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 1.40mm-2.15mm  
 Wire Size AWG 18, 20  
 Wire Size mm<sup>2</sup> 0.50-1.00

**Electrical**

Current - Maximum per Contact 12.0A



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
Prop65	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[64323](#) Series

**Mates With**

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

**Use With**

CMC Connector [64318](#) , [64319](#) , [64320](#) , [64321](#) , [64326](#)

Voltage - Maximum 14V DC

**Solder Process Data**

Lead-free Process Capability N/A

**Material Info**

**Reference - Drawing Numbers**

Application Specification AS-64318-002-001, AS-64318-002-CH-001,  
AS-64318-002-FR-001, AS-64318-002-SP-001,  
AS-64319-002-001, AS-64319-002-CH-001,  
AS-64319-002-FR-001, AS-64319-002-SP-001,  
AS-64323-001-001, AS-64323-001-CH-001,  
AS-64323-001-FR-001, AS-98420-001-001,  
AS-98420-001-CH-001, AS-98420-001-FR-001,  
AS-98420-001-SP-001, AS-98420-002-001,  
AS-98420-002-CH-001, AS-98420-002-FR-001,  
AS-98420-002-SP-001

Packaging Specification PK-98915-001-001

Product Specification PS-64319-002-001

Sales Drawing SD-64323-001-000

This document was generated on 09/12/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**