


www.vishay.com

Vishay Semiconductors

Optocoupler, Phototransistor Output, AC Input, SOP-4L, Long Mini-Flat Package



DESCRIPTION

The TCLT1600 consists of a phototransistor optically coupled to 2 gallium arsenide infrared-emitting diodes in an SOP 4-pin wide body package.


AGENCY APPROVALS

- UL1577, file no. E76222
- CSA 22.2 bulletin 5A, double protection
- DIN EN 60747-5-2 (VDE 0884)/DIN EN 60747-5-5 (pending), available with option 1
- BSI IEC 60950; IEC 60065

FEATURTES

- Low profile package
- Extra low coupling capacity typical 0.2 pF
- High common mode rejection
- AC input






• Creepage distance > 8 mm

· Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Switch-mode power supplies
- · Line receiver
- Computer peripheral interface
- Microprocessor system interface
- · Reinforced isolation provides circuit protection against electrical shock (safety class II)
- · Circuits for safe protective separation against electrical shock according to safety class II (reinforced isolation):
 - for appl. class I to IV at mains voltage ≤ 300 V
 - for appl. class I to III at mains voltage ≤ 600 V according to DIN EN 60747-5-2 (VDE 0884)





ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT				
INPUT								
Forward current		I _F	± 60	mA				
Forward surge current	t _p ≤ 10 μs	I _{FSM}	± 1.5	Α				
Power dissipation		P _{diss}	100	mW				
Junction temperature		Tj	125	°C				
OUTPUT								
Collector emitter voltage		V _{CEO}	70	V				
Emitter collector voltage		V _{ECO}	7	V				
Collector current		I _C	50	mA				
Collector peak current	$t_p/T = 0.5, t_p \le 10 \text{ ms}$	I _{CM}	100	mA				
Power dissipation		P _{diss}	150	mW				
Junction temperature		Tj	125	°C				
COUPLER								
Total power dissipation		P _{tot}	250	mW				
Operating ambient temperature range		T _{amb}	-55 to +100	°C				
Storage temperature range		T _{stg}	-55 to +125	°C				
Soldering temperature (1)		T _{sld}	260	°C				

Notes

www.vishay.com

⁽¹⁾ Wave soldering three cycles are allowed. Also refer to "Assembly Instruction" (www.vishay.com/doc?80054).

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT						
Forward voltage	$I_F = \pm 50 \text{ mA}$	V_{F}	-	1.25	1.6	V
Junction capacitance	$V_R = 0 V, f = 1 MHz$	C _j	-	50	-	pF
OUTPUT						
Collector emitter voltage	I _C = 1 mA	V_{CEO}	70	-	-	V
Emitter collector voltage	I _E = 100 μA	V_{ECO}	7	-	-	V
Collector ermitter leakage current	$V_{CE} = 20 \text{ V}, I_F = 0 \text{ A}$	I _{CEO}	-	10	100	nA
COUPLER						
Collector emitter saturation voltage	$I_F = \pm 10 \text{ mA}, I_C = 1 \text{ mA}$	V _{CEsat}	-	-	0.3	V
Cut-off frequency	V_{CE} = 5 V, I_F = ± 10 mA, R_L = 100 Ω	f _c	-	110	-	kHz
Coupling capacitance	f = 1 MHz	C _k	=	0.3	-	pF

Note

Minimum and maximum values are tested requierements. Typical values are characteristics of the device and are the result of engineering
evaluations. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER TEST CONDITION SYMBOL MIN. TYP. MAX. UNIT						
I _C /I _F	$V_{CE} = 5 \text{ V}, I_F = \pm 5 \text{ mA}$	CTR	80	-	300	%

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
maximum ratings for extended periods of the time can adversely affect reliability.



www.vishay.com

Vishay Semiconductors

SAFETY AND INSULATION RATINGS					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Partial discharge test voltage - routine test	100 %, t _{test} = 1 s	V _{pd}	2	kV	
Partial discharge test voltage -	$t_{Tr} = 60 \text{ s}, t_{test} = 10 \text{ s},$	V _{IOTM}	8	kV	
lot test (sample test)	(see figure 2)	V _{pd}	1.68	kV	
Isolation test voltage (RMS)		V _{ISO}	5000	V_{RMS}	
Insulation resistance	V _{IO} = 500 V	R _{IO}	10 ¹²	Ω	
	V _{IO} = 500 V, T _{amb} = 100 °C	R _{IO}	10 ¹¹	Ω	
	V _{IO} = 500 V, T _{amb} = 150 °C (construction test only)	R _{IO}	10 ⁹	Ω	
Forward current		I _{si}	130	mA	
Power dissipation		P _{SO}	265	mW	
Rated impulse voltage		V _{IOTM}	8	kV	
Safety temperature		T _{si}	150	°C	
Clearance distance			8.00	mm	
Creepage distance			8.00	mm	
Insulation distance (internal)			0.40	mm	

Note

 According to DIN EN 60747-5-2 (VDE 0884) (see figure 2). This optocoupler is suitable for safe electrical isolation only within the safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.




Fig. 1 - Derating Diagram




Fig. 2 - Test Pulse Diagram for Sample Test according to DIN EN 60747-5-2; IEC60747-5-5

SWITCHING CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Delay time	V_S = 5 V, I_C = 2 mA, R_L = 100 Ω , (see figure 3)	t _d	-	3	-	μs
Rise time	V_S = 5 V, I_C = 2 mA, R_L = 100 Ω , (see figure 3)	t _r	-	3	-	μs
Turn-on time	V_S = 5 V, I_C = 2 mA, R_L = 100 Ω , (see figure 3)	t _{on}	-	6	-	μs
Storage time	V_S = 5 V, I_C = 2 mA, R_L = 100 Ω , (see figure 3)	t _s	-	0.3	-	μs
Fall time	V_S = 5 V, I_C = 2 mA, R_L = 100 Ω , (see figure 3)	t _f	-	4.7	-	μs
Turn-off time	V_S = 5 V, I_C = 2 mA, R_L = 100 Ω , (see figure 3)	t _{off}	-	5	-	μs
Turn-on time	V_S = 5 V, I_F = 10 mA, R_L = 1 k Ω , (see figure 4)	t _{on}	-	9	-	μs
Turn-off time	$V_S = 5 \text{ V}, I_F = 10 \text{ mA}, R_L = 1 \text{ k}\Omega,$ (see figure 4)	t _{off}	-	10	-	μs



www.vishay.com

Vishay Semiconductors




Fig. 3 - Test Circuit, Non-Saturated Operation




Fig. 4 - Test Circuit, Saturated Operation





Fig. 5 - Switching Times




Vishay Semiconductors

PACKAGE DIMENSIONS (in millimeters)



PACKAGE MARKING



TAPE AND REEL DIMENSIONS (in millimeters)




Fig. 6 - Reel Dimensions (3000 units per reel)




Fig. 7 - Tape Dimensions





Vishay Semiconductors

SOLDER PROFILE




Fig. 8 - Lead (Pb)-free Reflow Solder Profile according to J-STD-020

HANDLING AND STORAGE CONDITIONS

ESD level: HBM class 2 Floor life: unlimited

Conditions: T_{amb} < 30 °C, RH < 85 %

Moisture sensitivity level 1, according to J-STD-020



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000