#LAB #EC_LED T26 5 NON-DIM 824 230V E14_AC3214

#2021-08-18

EU Declaration of Conformity



Document number: Manufacturer or representative: Address:	2021 / 9C1-4069702-EN-00 LEDVANCE GmbH Parkring 29-33
Brand name or trade mark:	85748 Garching Germany OSRAM
Product type:	Self-ballasted LED lamp
Product designation:	CLA/B/P;LED T26;CLGLOBE125
	See attached list

The designated product(s) is (are) in conformity with the relevant Union harmonisation legislation:

\boxtimes	2014/35/EU and amendments	Directive of the European Parliament and of the Council of 26 February 2014 on the harmonisation of the laws of the Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits
\boxtimes	2014/30/EU and amendments	Directive of the European Parliament and of the Council of 26 February 2014 on the harmonisation of the laws of the Member States relating to electromagnetic compatibility
\boxtimes	2009/125/EC and amendments, incl.	Directive of the European Parliament and of the Council of 21 October 2009 establishing a framework for the setting of ecodesign requirements for energy-related product
\boxtimes	2019/2020 and amendments	Commission Regulation (EU) 2019/2020 of 1 October 2019 laying down ecodesign requirements for light sources and separate control gears pursuant to Directive 2009/125/EC of the European Parliament and of the Council
	2019/2015 and amendments	Commission Delegated Regulation (EU) 2019/2015 of 11 March 2019 supplementing Regulation (EU) 2017/1369 of the European Parliament and of the Council with regard to energy labelling of light sources and repealing Commission Delegated Regulation (EU) No 874/2012
	2011/65/EU and amendments	Directive of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment
	2014/53EU and amendments	Directive of the European Parliament and of the Council of 16 April 2014 on the harmonisation of the laws of the Member States relating to the making available on the market of radio equipment and repealing Directive 1999/5/EC

Last two digits of the year in which the CE marking was affixed: 21

Place and date of signatures: July 22,2021

Signatures:

Quality Management

Quality Assurance

Names: Scheyer Yannick

Shufen Chen

Customer service contact: LEDVANCE GmbH, Steinerne Furt 62, 86167 Augsburg, Deutschland

This declaration of conformity is issued under the sole responsibility of the manufacturer or representative. It certifies compliance with the indicated Directives, but implies no warranty of properties

#2021-08-18 #

#RL-Released

9C1 4069702-EN-00

Document number: 2021 / 9C1-4069702-EN-00

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive 2014/35/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

DEIOW	applies.	
	EN 60155: 1995 + A1:1995 + A2:2007	Glow-starters for fluorescent lamps
	EN 60432-1: 2000 + A1:2005 + A2:2012	Incandescent lamps — Safety specifications — Part 1: Tungsten filament lamps for domestic and similar general lighting purposes
	EN 60432-2: 2000 + A1:2005 + A2:2012	Incandescent lamps — Safety specifications — Part 2: Tungsten halogen lamps for domestic and similar general lighting purposes
	EN 60432-3: 2013	Incandescent lamps — Safety specifications — Part 3: Tungsten halogen lamps (non-vehicle)
	EN 60598-1: 2015 + A1:2018	Luminaires — Part 1: General requirements and tests
	EN 60598-2-1: 1989	Luminaires — Part 2-1: Particular requirements — Fixed general purpose luminaires
	EN 60598-2-2: 2012	Luminaires — Part 2-2: Particular requirements — Recessed luminaires
	EN 60598-2-3: 2003 + A1:2011	Luminaires — Part 2-3: Particular requirements — Luminaires for road and street lighting
	EN 60598-2-4: 2018	Luminaires — Part 2-4: Particular requirements — Portable general purpose luminaires
	EN 60598-2-5: 2015	Luminaires — Part 2-5: Particular requirements — Floodlights
	EN 60598-2-6: 1994 + A1:1997	Luminaires — Part 2-6: Particular requirements — Luminaires with built-in transformers for filament lamps
	EN 60598-2-7: 1989 + A2:1996 + A13:1997	Luminaires — Part 2-7: Particular requirements — Portable luminaires for garden use
	EN 60598-2-8: 2013	Luminaires — Part 2-8 : Particular requirements — Handlamps
	EN 60598-2-10: 2003	Luminaires — Part 2-10: Particular requirements — Portable luminaires for children
	EN 60598-2-12: 2013	Luminaires — Part 2-12: Particular requirements — Mains socket-outlet mounted nightlights
	EN 60598-2-13: 2006 + A1 2012	Luminaires — Part 2-13: Particular requirements — Ground recessed luminaires
	EN 60598-2-20: 2015	Luminaires — Part 2-20: Particular requirements — Lighting chains
	EN 60598-2-22: 2014	Luminaires — Part 2-22: Particular requirements — Luminaires for emergency lighting
	EN 60598-2-24: 2013	Luminaires - Part 2-24: Particular requirements - Luminaires with limited surface temperatures
	EN 60950-1: 2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013	Information technology equipment – Safety – Part 1: General requirements
	EN 60968: 2015	Self-ballasted lamps for general lighting services — Safety requirements
	EN 61195: 1999 + A1:2013 + A2:2015	Double-capped fluorescent lamps — Safety specifications

1051b

#LAB #EC_LED T26 5 NON-DIM 824 230V E14_AC3214

Document number: 2021 / 9C1-4069702-EN-00

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive 2014/35/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

applie	53.	
	EN 61199: 2011 + A2:2015	Single-capped fluorescent lamps — Safety specifications
	EN 61347-1: 2015	Lamp controlgear — Part 1: General and safety requirements
	EN 61347-2-1: 2001 + A1:2006 + A2:2014	Lamp controlgear — Part 2-1: Particular requirements for starting devices (other than glow starters)
	EN 61347-2-2: 2012	Lamp controlgear — Part 2-2: Particular requirements for d. c. or a. c. supplied electronic step-down convertors for filament lamps
	EN 61347-2-3: 2011	Lamp controlgear — Part 2-3: Particular requirements for a. c. and/or d. c. supplied electronic ballasts for fluorescent lamps
	EN 61347-2-7: 2012	Lamp controlgear — Part 2-7: Particular requirements for battery supplied electronic controlgear for emergency lighting (self-contained)
	EN 61347-2-8: 2001 + A1:2006	Lamp controlgear — Part 2-8: Particular requirements for ballasts for fluorescent lamps
	EN 61347-2-9: 2013	Lamp controlgear — Part 2-9: Particular requirements for ballasts for discharge lamps (excluding fluorescent lamps)
	EN 61347-2-10: 2001 + A1:2009	Lamp controlgear — Part 2-10: Particular requirements for electronic invertors and convertors for high-frequency operation of cold start tubular discharge lamps (neon tubes)
	EN 61347-2-11: 2001	Lamp controlgear — Part 2-11: Particular requirements for miscellaneous electronic circuits used with luminaires
	EN 61347-2-12: 2005 + A1:2010	Lamp controlgear — Part 2-12: Particular requirements for d. c. or a. c. supplied electronic ballasts for discharge lamps (excluding fluorescent lamps)
	EN 61347-2-13: 2014	Lamp controlgear — Part 2-13: Particular requirements for d. c. or a. c. supplied electronic controlgear for LED modules
	EN 61549: 2003 + A1:2005 + A2:2010 + A3:2012	Miscellaneous lamps
	EN 62031: 2008 + A1:2013 + A2:2015	LED modules for general lighting — Safety specifications
	EN 62034: 2012	Automatic test systems for battery powered emergency escape lighting
	EN 62035: 2014	Discharge lamps (excluding fluorescent lamps) — Safety specifications
	EN 62368-1: 2014	Audio/video, information and communication technology equipment – Part 1: Safety requirements

#LAB #EC_LED T26 5 NON-DIM 824 230V E14_AC3214

#2021-08-18 #

#RL-Released

9C1 4069702-EN-00

Document number: 2021 / 9C1-4069702-EN-00

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive 2014/35/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

\boxtimes	EN 62493: 2015	Assessment of lighting equipment related to human exposure to electromagnetic fields
	EN 62532: 2011	Fluorescent induction lamps — Safety specifications
\boxtimes	EN 62560: 2012 + A1:2015+ A11:2019	Self-ballasted LED-lamps for general lighting services by voltage > 50 V — Safety specifications
	EN 62838: 2016	LEDsi lamps for general lighting services with supply voltages not exceeding 50 V a.c. r.m.s. or 120 V ripple free d.c Safety specifications Consumer goods with a voltage below 50 V are dealt with by the General Product Safety Directive (GPSD) 2001/95/EC
	EN 60669-2-1: 2004 + A1:2009 + A12:2010	Switches for household and similar fixed electrical installations - Part 2-1: Particular requirements - Electronic switches (IEC 60669-2-1:2002, modified) / Corrected and reprinted in 2007-12
	EN 62471: 2008	Photobiological safety of lamps and lamp systems
	EN 62733: 2015	Programmable components in electronic lamp controlgear
	EN 62776: 2015	Double-capped LED lamps designed to retrofit linear fluorescent lamps - Safety specifications

EU Declaration of Conformity Annex

Document number: 2021 / 9C1-4069702-EN-00

The conformity of the designated product(s) with the provisions of the European **EMC Directive**, **2014/30/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

\boxtimes	EN IEC55015: 2019+ A11:2020	Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment
\boxtimes	EN IEC 61000-3-2: 2019	Electromagnetic compatibility (EMC) — Part 3-2: Limits — Limits for harmonic current emissions (equipment input current ≤ 16 A per phase)
	EN 61000-3-3: 2013+ A1:2019	Electromagnetic compatibility (EMC) — Part 3-3: Limits — Limitation of voltage changes, voltage fluctuations and flicker in public low voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subjected to conditional connection
\boxtimes	EN 61547: 2009	Equipment for general lighting purposes — EMC immunity requirements
	EN 50498: 2010	Electromagnetic compatibility (EMC) – Product family standard for aftermarket electronic equipment in vehicles

EU Declaration of Conformity Annex

Document number: 2021 / 9C1-4069702-EN-00


The conformity of the designated product(s) with the provisions of the European **eco design (ERP) Directive 2009/125/EC** is given by the compliance with the following European Standard(s). If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

EN 62442-1: 2018	Energy performance of lamp controlgear - Part 1: Controlgear for fluorescent lamps - Method of measurement to determine the total input power of controlgear circuits and the efficiency of the controlgear
EN IEC 62442-2: 2019	Energy performance of lamp controlgear – Part 2: Controlgear for high intensity discharge lamps (excluding fluorescent lamps) – Method of measurement to determine the efficiency of the controlgear
EN IEC 62442-3: 2019	Energy performance of lamp controlgear – Part 3: Controlgear for halogen lamps and LED modules – Method of measurement to determine the efficiency of the controlgear

EU Declaration of Conformity Annex

Document number: 2021 / 9C1-4069702-EN-00

The conformity of the designated product(s) with the provisions of the European Directive **2011/65/EU (RoHS)** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.



9C1

#2021-08-18 #

#RL-Released

9C1 4069702-EN-00

EU Declaration of Conformity Annex

Document number: 2021 / 9C1-4069702-EN-00

The conformity of the designated product(s) with the provisions of the European $\ensuremath{\textbf{Radio}}$ Equipment Directive 2014/53EU is given by the compliance with the following European Standard(s). If not elsewhere/otherwise indicated the edition/amendment as referenced below applies

EN 300 328 V2.1.1	Wideband transmission systems; Data transmission equipment operating in the 2,4 GHz ISM band and using wide band modulation techniques; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU
EN 300 440 V2.1.1&V2.2.	Short Range Devices (SRD) ; Radio equipment to be used in the 1GHz to 40GHz frequency range; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU
Draft ETSI EN 301 489-1 V2.2.0	Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 1: Common technical requirements; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU and the essential requirements of article 6 of Directive 2014/30/EU
Draft EN 301 489-3 V2.1.1	Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 3: Specific conditions for Short-Range Devices (SRD) operating on frequencies between 9 kHz and 246 GHz; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU
Draft ETSI EN 301 489-17 V3.2.0	Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 17: Specific conditions for Broadband Data Transmission Systems; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU
EN 62479: 2010	Assessment of the compliance of low-power electronic and electrical equipment with the basic restrictions related to human exposure to electromagnetic fields (10 MHz to 300 GHz)

EU Declaration of Conformity Attached list

Document number: 2021 / 9C1-4069702-EN-00

Product list:

AC32147	LED T26 5 NON-DIM 824 230V E14
AC32148	LED T26 55 NON-DIM 827 230V E14
AC32149	
AC32150	
AC32151	LED T26 25 NON-DIM 865 230V E14
AC32152	LED T26 40 NON-DIM 827 230V E14
AC32274	CLP 40 Act&Rel FIL 80 2700&4000 E14
AC32275	CLB 40 Act&Rel FIL 80 2700&4000 E14
AC32276	CLA 60 Act&Rel FIL 80 2700&4000 E27
AC32291	CLB 40 dim FIL 80 2700 E27
AC32292	CLP 40 dim FIL 80 2700 E27
AC32295	CLP 60 dim GL FR 80 2700 E14
AC32296	CLB 40 dim GL FR 80 2700 B22d
AC32297	CLP 40 dim GL FR 80 2700 E27
AC32298	CLP 40 dim GL FR 80 2700 B22d
AC32299	CLP 25 dim GL FR 80 2700 E27
AC32304	CLB 25 dim FIL 80 2700 E14
AC32305	CLP 40 dim GL FR 80 4000 E14
AC32306	CLA 40 dim GL FR 80 4000 E27
AC32307	CLP 60 dim GL FR 80 4000 E14
AC32315	CLP 40 dim FIL 80 4000 E27
AC32316	CLP 40 dim FIL 80 4000 E14
AC32317	CLP 60 dim FIL 80 2700 E14
AC32318	CLP 25 dim FIL 80 2700 E27
AC32319	CLP 25 dim FIL 80 2700 E14
AC32320	CLB 40 dim FIL 80 4000 E14
AC32324	CLB 40 dim GL FR 80 2700 E27
AC32330	CLP 25 dim GL FR 80 2700 E14
AC32331	CLB 25 dim GL FR 80 2700 E14
AC32333	CLA 40 dim FIL 80 2700 E27
AC32335	CLP 40 dim FIL 80 2700 E14
AC32336	CLB 40 dim FIL 80 2700 E14
AC32337	CLP 40 dim GL FR 80 2700 E14
AC32338	CLB 40 dim GL FR 80 2700 E14
AC32339	CLA 40 dim GL FR 80 2700 E27
AC32386	CLA 50 non-dim FIL Mirror Gold 80 2700 E27
AC32405	CLA 150 non-dim GL FR 80 2700 E27
AC32406	CLA 150 non-dim GL FR 80 4000 E27
AC32409	CLA 37 non-dim FIL Mirror Gold 80 2700 E27
AC32416	CLA 150 dim GL FR 80 2700 E27

#2S1 #XUHUA LIANG #LEDVANCE PLP(V)

- AC32815 CLGLOBE125 150 non-dim GL FR 80 2700 E27
- AC32816 CLGLOBE125 150 non-dim GL FR 80 4000 E27
- AC35012 CLA 200 non-dim FIL 80 2700 E27
- AC35013 CLA 200 non-dim FIL 80 4000 E27
- AC36769 CLA 150 non-dim GL FR 80 2700 B22d
- AC36770 CLA 150 non-dim GL FR 80 4000 B22d