

Data cable - IFS-USB-DATACABLE - 2320500

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Used for communicating between industrial PCs and Phoenix Contact devices with the 12-pos. IFS data port, such as QUINT UPS or TRIO UPS.



Product Description

Data cable for communication between the UPS CONF configuration software and the QUINT UPS-IQ and TRIO UPS uninterruptible power supply units.

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 599023
GTIN	4046356599023
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	85444290
Country of origin	Germany

Technical data

Dimensions

Fixed cable length	3 m
--------------------	-----

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C (-13 °F ... 158 °F)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (-40 °F ... 185 °F)

General

Connection 1	PC side
Connection method	USB 2.0 Fullspeed
Note	serial
Connection 2	Device side
Connection method	IFS data port

Standards and Regulations

Data cable - IFS-USB-DATACABLE - 2320500

Technical data

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2

Classifications

eCl@ss

eCl@ss 4.0	27040702
eCl@ss 4.1	27040702
eCl@ss 5.0	27242213
eCl@ss 5.1	27230209
eCl@ss 6.0	27230209
eCl@ss 7.0	27230209
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 3.0	EC001039
ETIM 4.0	EC000830
ETIM 5.0	EC001408
ETIM 6.0	EC001408

UNSPSC

UNSPSC 6.01	30211502
UNSPSC 7.0901	39121004
UNSPSC 11	39121004
UNSPSC 12.01	39121004
UNSPSC 13.2	39121004

Approvals

Approvals

Approvals

EAC / EAC / ABS / BV / DNV GL

Ex Approvals

Approval details

Data cable - IFS-USB-DATACABLE - 2320500

Approvals

EAC EAC-Zulassung

EAC RU C-DE.A*30.B00767

ABS <http://www.eagle.org/eagleExternalPortalWEB/15-GD1438179-PDA>

BV <http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials41516/A0BV>

DNV GL <https://www.dnvgl.com/61457-13HH>

mm ² /AWG/kcmil	6
Nominal current I _N	41 A
Nominal voltage U _N	500 V