



MicroThan<sup>+</sup>



SIZE	ART. NO.	EAN NO.
6	9121-6	7392626020887
7	9121-7	7392626020894
8	9121-8	7392626020900
9	9121-9	7392626020917
10	9121-10	7392626020924
11	9121-11	7392626020931

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

## TEGERA® 9121

Cut resistant glove, half-lined, 0,5 mm Microthan<sup>+</sup>, diamond grip pattern, polyester, cut resistance level 3, KEVLAR<sup>®</sup> fiber, Cat. II, black, grey, yellow, cut protection in the palm only, reinforced seams, chrome free, Velcro<sup>®</sup>

### PROPERTIES

Good fingertip sensitivity, flexible, durable, excellent grip, perfect fit, extra comfortable

### SPECIFICATION

TYPE OF GLOVE Cut resistant gloves

CATEGORY Cat. II

CUT RESISTANCE (COUP) Cut resistance level 3

SIZE RANGE (EU) 6, 7, 8, 9, 10, 11

PALM MATERIAL Microthan<sup>+</sup>

PALM THICKNESS 0,5 mm

BACK MATERIAL Polyester

LINING Half-lined

LINING MATERIAL KEVLAR<sup>®</sup> fiber

DEXTERITY 5

GRIP PATTERN Diamond grip pattern

FASTENING Velcro<sup>®</sup>

LENGTH RANGE 207-243 mm

COLOUR Black, grey, yellow

PAIRS PER PACKAGE/CARTON 6/60

DISPLAY Hook with hangtag

OUTER MATERIAL SPECIFICATION Polyurethane, nylon, polyester

INNER MATERIAL SPECIFICATION Para-aramid



CE Cat. II



## TEGERA® 9121

### FEATURES

Cut protection in the palm only, cut resistant according to EN 388 level 3 (5), chrome free, reinforced index finger, reinforced seams, reinforced fingertips, pre-curved fingers, specially designed thumb, short model, ergonomically shaped, reflector, specially designed details

### PRIMARY PROTECTION

Prevents risk of: chrome allergy, cut injuries, abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping

### PRIMARY ENVIRONMENTS OF USE

Cut risk environments, dark environments, slippery environments, dry environments, moist environments, oil and greasy environments, dirty environments

### PRIMARY AREAS OF USE

Fine assembly, machine operating, building and construction, carpentry, installation work, HVAC installation, sheet-metal work, construction, soil preparation, engineering, transport work, machine driving, warehouse work, airport work, metalwork, mining, forest work, agricultural work, gardening, repair work, security- and police work, paper industry work

### TYPE OF WORK

Light weight

2(3)

**ejendals**  
PROTECTING HANDS AND FEET

#### EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

## TEGERA® 9121

### EC TYPE EXAMINATION

Notified Body: 0321 SATRA Technology Centre, Wyndham Way, Telford Way, Kettering, Northamptonshire, NN16 8SD, United Kingdom

### COMPLIANCE DESCRIPTION

EN 420:2003 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks


Property	Level Achieved	(Maximum Performance)
A) Resistance to wear (No. of revolutions)	0	(4)
B) Resistance to cutting (Index)	3	(5)
C) Tear resistance (Newton)	2	(4)
D) Puncturing resistance (Newton)	1	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).

Level of protection	1	2	3	4	5
A) Resistance to wear (No. of revolutions)	100	500	2000	8000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	



**CE** Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2016-11-25

**ejendals**  
PROTECTING HANDS AND FEET

**EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com