

## Supra S drill chuck, keyless clamping

Keyless clamping; drill chuck taper in accordance with DIN ISO 239-B



### Application:

For clamping and releasing drill bits quickly without a key.

### Execution:

- Industrial version for hand-guided machines.
- Automatic retightening during drilling proportionate to the cutting force.
- With internal taper chuck in accordance with DIN 238.
- All parts are interchangeable.

### Advantage:

- No tools required for operation, allowing for fast retooling.
- For day-to-day industrial use.
- Very strong and resistant to wear.

### Delivery:

1x 1.0-13 mm/B 12 drill chuck.



<b>Art. no.</b>	<b>21301 090</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	87 1047
<b>Min./max. clamping width</b>	1-13 mm
<b>Suitable for taper</b>	B 16
<b>Outer diameter</b>	40.2 mm
<b>Gross Weight</b>	0.605 kg
<b>Product Group</b>	201

### EAN

4019208014449