

## NEOSTAR permanent round magnets

With radial pole pitch.



### Application:

For round and ring-shaped workpieces.

### Execution:


- High magnetic force.
- Concentric rings allow easy alignment of workpieces.
- The magnetic field can be infinitely adjusted up to diameter 300 mm.
- Standard design without through-bore in the centre.

### Advantage:

- Balanced design.
- Suitable for high rotation speeds.
- Infinitely variable adjustment of adhesive force.

### Delivery:

1x permanent round magnet; incl. hex key.



<b>Art. no.</b>	<b>24376 200</b>
<b>Brand</b>	SAV WALKER HAGOU
<b>Manufacturer Part Number</b>	244.06-200
<b>Clamping plate diameter</b>	200 mm
<b>Height</b>	57 mm
<b>Centring diameter</b>	60 mm
<b>Magnet-free zone</b>	28 mm
<b>Max. clearance hole</b>	30 mm
<b>Large pitch circle</b>	180 mm
<b>Fastening thread</b>	M6
<b>Small pitch circle</b>	110 mm
<b>Pole plate thickness</b>	20 mm
<b>Wear of pole surface</b>	5 mm
<b>Number of magnetic terminals</b>	12 PCS
<b>Nominal adhesive strength</b>	100 N/cm <sup>2</sup>
<b>Weight</b>	13 kg
<b>Gross Weight</b>	13.548 kg
<b>Product Group</b>	230