


Switched-Mode Power Supply, 1-Phase

EPSITRON® PRO Power



- Primary switch mode power supply unit with PowerBoost and TopBoost
- Stand-by input for switching off the output and minimizing power consumption
- DC OK contact for output monitoring
- Parallel operation, series connection possible
- Prepared for class I equipment
- Natural convection cooling when horizontally mounted
- Enclosed for use in switchgear cabinets
- Electrically isolated output voltage (SELV) acc. to EN 60950-1/UL 60950

Technical Data

Input:

Nominal input voltage V_i nom	110 ... 240 VAC
Input voltage range	85 ... 264 VAC; 120 ... 350 VDC
Frequency	50 Hz ... 60 Hz
Input current I_i	1.2 A at 230 VAC and 10 ADC
Discharge current	1 mA typ.
Inrush current	$\leq I_e$ (active inrush current limitation)
Mains failure hold-up time	24 ms typ. at 230 VAC

Output:

Nominal output voltage V_o nom	24 VDC (SELV)
Output voltage range	22... 29.5 VDC adjustable
Output current I_o	10 A at 24 V DC
PowerBoost	20 ADC (for 4 sec.); 15 ADC (for another 2 sec.)
TopBoost	60 ADC (for 25 ms)
Factory preset	24 VDC
Adjustment accuracy	1%
Residual ripple	< 70 mV (peak-to-peak)
Current limitation	1.1 x I_o typ.
Overload behavior	Constant current
Operational indication	LED green (DC O.K.), LED red (error)
Signaling	Relay contact DC O.K. (changeover contact)

Efficiency / power losses:

Efficiency	91.8 % typ.
Power loss P_V	0.8 W (stand-by) / 3.5 W (no load) / 19.7 W (rated load)

Fuse protection:

Internal fuse	T 6.3 A / 250 V
External fuse	C10 or B16 circuit breakers
	An external DC fuse is required for the DC input voltage
	Transient overvoltage protection: Varistor

Description	Item No.	Pack. Unit
Switched-Mode Power Supply, 24 V DC / 10 A	787-832	1

Technical Data

Environmental requirements:

Ambient operating temperature	-25 °C ... +70 °C
Storage temperature	-25 °C ... +85 °C
Rel. humidity	30 % ... 85 % (no condensation)
Derating	-3 % / K (> 50 °C)
Degree of pollution	2 (acc. to EN 50178)
Climatic category	3K3 (acc. to EN 60721)

Safety and protection:

Test voltage pri.-sec./ pri.-gr. / sec.-gr.	4.2 kV DC / 2.2 kV DC / 0.7 kV DC
Protection class	Prepared for class I equipment
Degree of protection	IP20 (acc. to EN 60529)
Overvoltage protection	via varistor at primary circuit
Short circuit protection	yes
No-load proof	yes
Feedback voltage	max. 35 VDC
Parallel operation	yes
Series connection	yes

Connection and type of mounting:

Wire connection	Input/Output: WAGO 231 Series Signalling: WAGO 733 Series
Cross sections	Input/Output: 0.08 mm ² ... 2.5 mm ² / AWG 28 ... 12 Signalling: 0.08 mm ² ... 0.5 mm ² / AWG 28 ... 20
Strip lengths	Input/Output: 8 ... 9 mm / 0.33 in Signalling: 5 ... 6 mm / 0.22 in
Type of mounting	DIN-rail mounting (EN 60715) in 2 positions

Dimensions and weight:

Dimensions (mm) W x H x L	57 x 163 x 179
Weight	Height from upper-edge of DIN 35 rail 1485 g

Standards and approvals:

Standards/Specifications	EN 60950, EN 61204-3, UL 60950, UL 508
--------------------------	---