## **Reflex Sensor**

with Background Suppression

# HB03PDT7K

Part Number



- Adjustable switching distance
- Electronic background suppression
- Enclosed in M8 housing
- Red light

#### **Technical Data**

Optical Data				
Range	30 mm			
Adjustable Range	1030 mm			
Switching Hysteresis	< 10 %			
Light Source	Red Light			
Service Life (T = +25 °C)	100000 h			
Max. Ambient Light	10000 Lux			
Light Spot Diameter	2 mm			
Electrical Data				
Supply Voltage	1030 V DC			
Current Consumption (Ub = 24 V)	< 25 mA			
Switching Frequency	600 Hz			
Response Time	833 μs			
Temperature Drift	< 5 %			
Temperature Range	-2560 °C			
Switching Output Voltage Drop	< 2,5 V			
PNP Switching Output/Switching Current	100 mA			
Short Circuit Protection	yes			
Reverse Polarity Protection	yes			
Overload Protection	yes			
Protection Class	III			
Mechanical Data				
Setting Method	Teach-In			
Housing Material	Stainless Steel			
Full Encapsulation	yes			
Degree of Protection	IP67			
Connection	M8 × 1; 4-pin			
Cable Length	20 cm			
PNP NC	•			
Connection Diagram No.	106			
Control Panel No.	B1			
Suitable Connection Equipment No.	7			
Suitable Mounting Technology No.	200			


These sensors detect distance by measuring angles. They are particularly good at recognizing objects in front of any background. The color, shape and surface characteristics of the object have practically no influence on sensor switching performance.



#### **Complementary Products**

PNP-NPN Converter BG7V1P-N-2M










06 = Teach Button



Legen	nd		PT	Platinum measuring resistor	ENARS42	Encoder A/Ā (TTL)	
+	Supply Voltage +		nc	not connected	ENBRS42	Encoder B/B (TTL)	
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A	
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B	
Α	Switching Output	(NO)	W	Trigger Input	Amin	Digital output MIN	
Ā	Switching Output	(NC)	W -	Ground for the Trigger Input	Амах	Digital output MAX	
V	Contamination/Error Output	(NO)	0	Analog Output	Аок	Digital output OK	
V	Contamination/Error Output	(NC)	0-	Ground for the Analog Output	SY In	Synchronization In	
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT	
Т	Teach Input		Awv	Valve Output	OLT	Brightness output	
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance	
S	Shielding		b	Valve Control Output 0 V	rsv	reserved	
RxD	Interface Receive Path		SY	Synchronization	Wire Co	/ire Colors according to DIN IEC 757	
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black	
RDY	Ready		E+	Receiver-Line	BN	Brown	
GND	Ground		S+	Emitter-Line	RD	Red	
CL	Clock		±	Grounding	OG	Orange	
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow	
•	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green	
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue	
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey	
Signal			Mag	Magnet activation	WH	White	
BI_D+/-	Ethernet Gigabit bidirect, data	line (A-D)	RES	Input confirmation	PK	Pink	
	Encoder 0-pulse 0-0 (TTL)		EDM	Contactor Monitoring	GNYE	Green/Yellow	

### **Switching Distance Deviation**

Typical characteristic curve based on white, 90 % remission

