Fiber-Optic Cable Sensor


ODX202P0107

Part Number



- Key potentiometer, teach-in
- Large detection and working range
- Recognition of transparent objects
- Reflex and through-beam operation mode are possible

wenglor fiber-optic cables are connected to these sensors. The easy to use teach-in function allows for fine sensor adjustment, so that even transparent objects can be reliably recognized in through-beam mode operation. The scanning width is automatically adapted to each individual application via external teach-in. The sensors can be easily mounted to standard DIN rails.




Technical Data

| Optical Data | |
|--|--------------------|
| Switching Hysteresis | < 15 % |
| Light Source | Red Light |
| Wavelength | 660 nm |
| Service Life (T = +25 °C) | 100000 h |
| Max. Ambient Light | 10000 Lux |
| Electrical Data | |
| Supply Voltage | 1030 V DC |
| Current Consumption (Ub = 24 V) | < 40 mA |
| Switching Frequency | 2 kHz |
| Response Time | 250 μs |
| On-/Off-Delay | 0200 ms |
| Temperature Drift | < 10 % |
| Temperature Range | -2560 °C |
| Switching Output Voltage Drop | < 2,5 V |
| Switching Output/Switching Current | 200 mA |
| Short Circuit Protection | yes |
| Reverse Polarity Protection | yes |
| Overload Protection | yes |
| Teach Mode | NT, MT, ZT, DT, TP |
| Protection Class | III |
| Mechanical Data | |
| Setting Method | Teach-In |
| Housing Material | Plastic |
| Full Encapsulation | yes |
| Degree of Protection | IP65 |
| Connection | M8 × 1; 4-pin |
| DIN-Rail mounting | 35 mm |
| Safety-relevant Data | |
| MTTFd (EN ISO 13849-1) | 1494,72 a |
| Contamination Output | • |
| Configurable as PNP/NPN/Push-Pull | |
| Switchable to NC/NO | |
| Connection Diagram No. | 771 |
| Control Panel No. | X1 |
| Suitable Connection Equipment No. | 7 |
| Suitable Fiber-Optic Cable Adapter No. | 03 |
| | |


Complementary Products

Glass Fiber-Optic Cable
Plastic Fiber-Optic Cable






Ctrl. Panel



- 01 = Switching Status Indicator
- 02 = Contamination Warning
- 07 = Selector Switch
- 24 = Plus Button
- 25 = Minus Button



| _egen | a | | PT | Platinum measuring resistor | ENA | RS422 Encoder A/Ā (TTL) |
|----------|-----------------------------------|-----------|-------|--------------------------------|------|-----------------------------------|
| + | Supply Voltage + | | nc | not connected | ENE | RS422 Encoder B/B (TTL) |
| - | Supply Voltage 0 V | | U | Test Input | ENA | Encoder A |
| ~ | Supply Voltage (AC Voltage) | | Ū | Test Input inverted | ENE | Encoder B |
| Α | Switching Output (| NO) | W | Trigger Input | Ами | Digital output MIN |
| Ā | Switching Output (| NC) | W - | Ground for the Trigger Input | Ама | x Digital output MAX |
| ٧ | Contamination/Error Output (| NO) | 0 | Analog Output | Аок | Digital output OK |
| V | Contamination/Error Output (| NC) | 0- | Ground for the Analog Output | SY | n Synchronization In |
| E | Input (analog or digital) | | BZ | Block Discharge | SY | OUT Synchronization OUT |
| Т | Teach Input | | Awv | Valve Output | OLT | Brightness output |
| Z | Time Delay (activation) | | а | Valve Control Output + | М | Maintenance |
| S | Shielding | | b | Valve Control Output 0 V | rsv | reserved |
| RxD | Interface Receive Path | | SY | Synchronization | Wire | e Colors according to DIN IEC 757 |
| TxD | Interface Send Path | | SY- | Ground for the Synchronization | BK | Black |
| RDY | Ready | | E+ | Receiver-Line | BN | Brown |
| GND | Ground | | S+ | Emitter-Line | RD | Red |
| CL | Clock | | ÷ | Grounding | OG | Orange |
| E/A | Output/Input programmable | | SnR | Switching Distance Reduction | YE | |
| 0 | IO-Link | | Rx+/- | Ethernet Receive Path | GN | Green |
| PoE | Power over Ethernet | | Tx+/- | Ethernet Send Path | BU | Blue |
| IN | Safety Input | | Bus | Interfaces-Bus A(+)/B(-) | VT | Violet |
| OSSD | Safety Output | | La | Emitted Light disengageable | GY | Grey |
| Signal | Signal Output | | Mag | Magnet activation | WH | White |
| BI_D+/- | Ethernet Gigabit bidirect. data I | ine (A-D) | RES | Input confirmation | PK | Pink |
| ENors422 | Encoder 0-pulse 0-0 (TTL) | | EDM | Contactor Monitoring | GN | YE Green/Yellow |









