

Collet chucks type ER32 in accordance with DIN 6499 A

HP = high precision, concentricity < 5 µm

ATORN[®]

Application

For use on precision collet chucks

Advantage

- Higher concentricity extends tool life

Art. no.	23388 056
Collet type	ER 32
Clamping diameter	3.5 mm
Min./max. clamping range	2-20 mm
Outer diameter	33 mm
Length	40 mm
Clamping bypass	-0.5 mm



EAN-Code

405029363025 1