

356114-1 ✓ ACTIVE

AMP

TE Internal #: 356114-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, MIL Spec, TE Certification, Manual / Pneumatic

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **MIL Spec**

TE Certification: **Yes**

**Features**

**Other**

Crimp Form-Wire Barrel Type	Closed Barrel - 4 Indent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	MIL Spec
TE Certification	Yes
Power Technology Type	Manual, Pneumatic
Tooling Type	Four Indent Hand Tool

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed















Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 193991-4 PIN ASSY. TPE XII</p>	 <p>TE Part # 193458-1 SKT ASSEMBLY, POWER #8 AWG</p>	 <p>TE Part # 193535-1 SKT ASSY.,POWER, #12-14 AWG</p>	 <p>TE Part # 193642-1 PIN ASSY.,POWER, #10 AWG</p>
 <p>TE Part # 193990-2 SKT ASSY,TYPE XII, #8 AWG</p>	 <p>TE Part # 193534-1 PIN ASSY, POWER ,12-14 AWG</p>	 <p>TE Part # 193842-1 SKT ASSY., 2MM, 12-14 AWG</p>	 <p>TE Part # 193841-1 PIN, 2MM, 12-14 AWG</p>
 <p>TE Part # 193796-1 PIN CONTACT - 2MM,10AWG</p>	 <p>TE Part # 193797-1 SKT ASSY - 2MM, 10 AWG</p>	 <p>TE Part # 193643-1 SKT ASSY.,POWER, #10-12 AWG</p>	 <p>TE Part # 194213-1 SKT,MNL,#12/14, LUBRICATED</p>



### Customers Also Bought



### Documents



**Datasheets & Catalog Pages**

[CERTI-CRIMPPII-Premium-August-1-1773864-7](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English