

90° manual deburring tool, HSS, triple cutter
for universal use up to 1000 N/mm²



Application

For producing 90° counterbores and for deburring up to 1000 N/mm².

Version

- profile-ground triple-edge countersink with radial relief

Advantage

- radial relief ensures optimum chip breaking
- innovative cutting geometry provides excellent cutting performance and good finish quality
- ergonomic plastic handle ensures good power transmission



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	●	●	○	○		●	●	●	●	●	●	●	○	○					

Art. No.	11511 112
Countersink angle	90 Degree
Cutting material	HSS
Surface	Uncoated
Number of cutting edges	3 PCS
Spot-facer diameter	12.4 mm

EAN-Code

4050293067736