

Revolution Series Finishing Tools
Outils de Finition - Série "Révolution"
Werkzeuge zur Oberflächenbearbeitung der Baureihe Revolution
Herramientas de Acabado Revolution
Utensili per la Finitura - Serie Revolution



Options



Piped-away exhaust kit, part no. **LG1-K284**
 Kit d'échappement canalisé réf. **LG1-K284**
 Abluft-Ableitsatz Teile Nr. **LG1-K284**
 Juego escape remoto no. **LG1-K284**
 Tubo scarico completo **LG1-K284**

Standard Equipment



- Internal wick lubricator.
- Graisseur incorporé.
- Integrierte Dochtöler.
- Engrasador incorporado.
- Ingrassatore a stoppino interno.
- Aluminum motor cap.
- Protection avant en alu.
- Motor-Aluminiumkappe.
- Tapa del motor en aluminio.
- Coperchio del motore in alluminio.
- Wraparound exhaust ports.
- Echappement profilé.
- Rückwärtige Abluftführung.
- Escapes remotos.
- Scarichi prolungati.
- Composite grip over aluminum housing.
- Revêtement composite sur corps robuste en alu.
- Griff aus Verbundwerkstoff über Aluminiumgehäuse.
- Empuñadura en composite sobre caja de aluminio.
- Presa in composito sopra cassa in alluminio.
- Integral trigger safety lock.
- Levier de sécurité.
- Drücker-Sicherheitsarretierung.
- Palanca de seguridad.
- Leva di sicurezza con bloccaggio.
- Rotatable angle head.
- Tête d'angle orientable.
- Variable Winkelkopfeinstellung.
- Cabezal giratorio en los modelos angulares.
- Testa a più posizionamenti sul modelli ad angolo.

Specifications at 90 psi – Caractéristiques à 6,2 bar – Technische Daten bezogen auf 6,2 bar – Especificaciones a 6,2 bar – Caratteristiche a 6,2 bar

Ref.	kWatt	1 min.							AIR	AIR
	kW	rpm	mm	mm	in	kg	mm	mm	in (NPT)	mm
STRAIGHT GRINDERS - MEULEUSES DROITES - GERADE SCHLEIFMASCHINEN - AMOLADORAS RECTAS - SMERIGLIATRICI DIRITTE										
325SC4	0.22	25000	Ø6 Erickson	–	–	0.37	152	–	1/4	10
330SC4	0.22	30000	Ø6 Erickson	–	–	0.37	152	–	1/4	10
335SC4	0.22	35000	Ø6 Erickson	–	–	0.37	152	–	1/4	10
325XC4	0.22	25000	Ø6 Erickson	–	–	0.57	229	–	1/4	10
330XC4	0.22	30000	Ø6 Erickson	–	–	0.57	229	–	1/4	10
ANGLE GRINDERS - MEULEUSES D'ANGLE - WINKELSCHLEIFMASCHINEN - AMOLADORAS ANGULARES - SMERIGLIATRICI AD ANGOLO										
312AC4	0.22	12000	Ø6 Erickson	–	–	0.51	156	64	1/4	10
314AC4	0.22	14000	Ø6 Erickson	–	–	0.51	156	64	1/4	10
320AC4	0.22	20000	Ø6 Erickson	–	–	0.51	156	64	1/4	10
312AG3	0.22	12000	–	Ø75	3/8"-24	0.63	159	64	1/4	10
314AG3	0.22	14000	–	Ø75	3/8"-24	0.63	159	64	1/4	10
320AG3	0.22	20000	–	Ø75	3/8"-24	0.63	159	64	1/4	10