

## Sliding door cabinets, height 1028 mm

With 2 full-width shelves, load capacity 100 kg per shelf

### Execution:

- Sturdy welded sheet steel construction, equipped with sliding doors
- With 2 full-width shelves made of sheet steel with support rails, height-adjustable in increments of 30 mm
- Doors can be locked simultaneously with a push-in cylinder lock, incl. 2 keys

### Advantage:

- The sliding-door cabinets can be used and combined as top-mounted cabinets for two HK drawer cabinets from system 550 S/700 S/800 S (width 722 mm).



<b>Art. no.</b>	<b>50051 701</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50051701
<b>Door design</b>	Full-sheet panel
<b>Height</b>	1028 mm
<b>Depth</b>	400 mm
<b>Width</b>	1444 mm
<b>With partition wall</b>	No
<b>Number of folder height</b>	2 PCS
<b>Number of shelves</b>	2 PCS
<b>Load-carrying capacity per shelf</b>	100 kg
<b>Number of drawers</b>	0 PCS
<b>Load-carrying capacity</b>	500 kg
<b>Lock type</b>	Cylinder lock
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	70.000 kg
<b>Product Group</b>	501

### EAN

4053625401529