

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Ethernet switch, five TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function. The multicast filter will block PROFINET PTCP-Delay traffic. EtherNet/IP™-based traffic will be prioritized over standard traffic.

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- QoS-prioritized (Quality of Service) messages
- Local diagnostic indicators with LEDs
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial Data

Item number	1071801
Packing unit	1 pc
Minimum order quantity	1 pc
Product Key	DNN113
GTIN	4055626752792
Weight per Piece (including packing)	277.3 g
Weight per Piece (excluding packing)	277.3 g
Customs tariff number	85176200
Country of origin	TW

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Technical Data

Dimensions

Width	28 mm
Height	110 mm
Depth	70 mm

Material specifications

Housing material	Aluminum
------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	5 (RJ45 ports)

Product properties

Type	Block design
Product type	Switch
MTTF	360.5 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

Switch functions

EtherNet/IP™ supported protocols	Ethernet/IP
Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
PROFINET conformance class	Conformance-Class A
MAC address table	1k
Status and diagnostic indicators	LEDs: U _S , link and activity per port
Additional functions	Autonegotiation

Security functions

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
-----------------	---

Electrical properties

Maximum power dissipation for nominal condition	4.44 W
Transmission medium	Copper

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Supply

Supply voltage	24 V DC
Supply voltage range	12 V DC ... 48 V DC
Power supply connection	Via COMBICON, max. conductor cross section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	345 mA (at 12 V DC)
Typical current consumption	185 mA (at U _S = 24 V DC)

Connection data

Connection method	Screw connection
Conductor cross section, rigid	0.2 mm ² ... 2.5 mm ²
Stripping length	7 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)

EMC data

Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B
	IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-4-4 (burst) Criterion B
	IEC 61000-4-5 (surge) Criterion B
	IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-4-8 (immunity to magnetic fields) Criterion A
	EN 55022 (emitted interference) Criterion A
Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2

LED signaling

Status display	LEDs: U _S , link and activity per port
----------------	---


Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE





1071801


<https://www.phoenixcontact.com/pc/products/1071801>

Approvals

 IECEE CB Scheme Approval ID: DK-88783-M1-UL		Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
				-	-

 EAC Approval ID: RU*-DE.*.B.00731/19	
--	--

 UL Listed Approval ID: FILE E 238705	
--	--

 cUL Listed Approval ID: FILE E 238705	
--	--

cULus Listed	
---------------------	--

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Classifications

ECLASS

ECLASS-9.0	19170106
ECLASS-10.0.1	19170402
ECLASS-11.0	19170402

ETIM

ETIM 8.0	EC000734
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Accessories

PCB connector

PCB connector - MSTB 2,5/ 3-ST - 1754465

<https://www.phoenixcontact.com/pc/products/1754465>



PCB connector, nominal cross section: 2.5 mm², color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, type of contact: Female connector, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/...-ST, pitch: 5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting: without, type of packaging: packed in cardboard

Surge protection device

Surge protection device - DT-LAN-CAT.6+ - 2881007

<https://www.phoenixcontact.com/pc/products/2881007>



Surge protection in accordance with Class E_A (CAT6_A), for Gigabit Ethernet (up to 10 Gbps), token ring, FDDI/CDDI, ISDN, and DS1. Suitable for Power over Ethernet (PoE++ / 4PPoE) "Mode A" and "Mode B". RJ45 attachment plug with separate grounding cable and ground connection snap-on foot for NS 35 DIN rails.

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Patch cable

Patch cable - FL CAT5 PATCH 0,5 - 2832263

<https://www.phoenixcontact.com/pc/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



Patch cable

Patch cable - FL CAT5 PATCH 1,0 - 2832276

<https://www.phoenixcontact.com/pc/products/2832276>

Patch cable, CAT5, assembled, 1 m



Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE

1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Patch cable

Patch cable - FL CAT5 PATCH 2,0 - 2832289

<https://www.phoenixcontact.com/pc/products/2832289>

Patch cable, CAT5, assembled, 2 m




Patch cable

Patch cable - NBC-R4AC-R4AC-IE8A/.../... - 1411854

<https://www.phoenixcontact.com/pc/products/1411854>

Patch cable, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, cable outlet: straight, Ethernet



Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE




1071801

<https://www.phoenixcontact.com/pc/products/1071801>

Patch cable

Patch cable - NBC-R4AC/10G-R4AC/10G-94F/2,0 - 1408360

<https://www.phoenixcontact.com/pc/products/1408360>




Patch cable, CAT6_A, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 2.0 m

Patch cable

Patch cable - NBC-R4AC/10G-R4AC/10G-94F/3,0 - 1408365

<https://www.phoenixcontact.com/pc/products/1408365>



Patch cable, CAT6_A, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 3.0 m

Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801


<https://www.phoenixcontact.com/pc/products/1071801>

DIN rail adapter

DIN rail adapter - FL DIN RA - 2891053

<https://www.phoenixcontact.com/pc/products/2891053>

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.




Dust protection

Dust protection - FL RJ45 PROTECT CAP - 2832991

<https://www.phoenixcontact.com/pc/products/2832991>

Dust protection caps for RJ45 socket



Industrial Ethernet Switch - FL SWITCH SFNB 5TX-PNE



1071801

<https://www.phoenixcontact.com/pc/products/1071801>

End clamp

End clamp - E/NS 35 N - 0800886

<https://www.phoenixcontact.com/pc/products/0800886>

End clamp, width: 9.5 mm, color: gray



Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com