



+  Mehr Anzeigen

ARTIKEL-NUMMER: 1015369

A800, klar, FB

Honeywell

Überblick

Artikelnummer

1015369

Produkttyp

Augen- und Gesichtsschutz

Programm

Brillen

Produktlinie

Einscheibenbrillen

Marke

Honeywell

Marke vorher bekannt als

PULSAFE

Branche

■ Industrie allgemein

Produktverwendung

A800 mit klarer und beschlagfreier Sichtscheibe zur Anwendung im Innenbereich

Schutz gegen allgemeine Gefahren und fliegende Teilchen (45 m/s)

Ideal geeignet für Anwendungen in geschlossenen Räumen im Baugewerbe, der verarbeitenden Industrie, in Ver- und Entsorgung, in der Biotechnologie, Labors, Reinräumen, im Schiffbau und in der Automobilindustrie.

Eigenschaften und Nutzen

Funktion

Ökonomische Komfort-Arbeitsschutzbrille Äußerst günstiges Modell für hohe Wirtschaftlichkeit im Unternehmen Kompaktes Design Sportliche Optik

Nutzen

Durch das kompakte Design sitzt die A800 auch bei schmalern Gesichtern komfortabel und sicher. Die sportliche Optik erhöht die Trageakzeptanz.

Funktion

Kratzfeste Polycarbonat-Sichtscheibe mit 9 Dioptrien Linsenkrümmung

Nutzen

Für verzerrungsfreie 180°-Rundumsicht

Funktion

Geschwungene, ergonomisch geformte Bügel mit weichen Polstern

Nutzen

Für eine sportliche Optik und mehr Tragekomfort

Funktion

Das weiche Nasenteil passt sich unterschiedlichen Nasenformen an.

Nutzen

Für zusätzlichen Tragekomfort und sicheren Sitz

Funktion

Beschlagfreie Sichtscheibe

Nutzen

Minimiert das Beschlagen auch unter extremen Bedingungen

Technische Beschreibung

Farbe Sichtscheibe

klar, VLT = 92 %

Beschichtung Sichtscheibe

FogBan (beschlagfrei/kratzfest)

Material der getönten Sichtscheibe

Polycarbonat

Rahmenfarbe

transparent

Zertifizierungen


 EU-Konformitätserklärung

EG-Kategorie PSA

14

Qualitätssicherung

ISO 9001 / 2000



EG-Zertifizierungsnummer


EC 1790

EG-Baumusterprüfbescheinigung


 EC Attestation

Nr. EG-Baumusterprüfbescheinigung

EC 1790




Leider sind momentan keine Bilder verfügbar.



EAN-Code

7312550153697



Verpackung

EC TYPE-EXAMINATION CERTIFICATE: 1790


Product description: - Personal Protective Spectacles

Product identification: - HONEYWELL A800

Manufacturer: Sperian Eye and Face Protection Inc.
10 Thurber Boulevard
Smithfield
RI 02917
U S A

When assessed and examined against harmonised standard EN166:2001 are found to be in conformity with Council Directive 89/686/EEC and associated amendments, relating to personal protective equipment.

Authorised EU Representative: - Sperian Protection Europe (SAS)
ZI Paris Nord II
33 Rue des Vanesses, BP 50 288
95958 Roissy CDG cedex
France

Signed 

Date: 31st March 2008

K J Warren, Manager, Certification Services

For and on behalf of INSPEC International Ltd.
(Notified Body No: 0194)

certificate invalid
if not embossed

For terms and conditions of issue, see page 2

Terms and Conditions

Reference Documents: -

- | | | | |
|------|----------------|---|--|
| i) | Test Report | - | ICS T3141-01-1 Issue 1. |
| ii) | Technical File | - | TF/1790 |
| iii) | Quality Plan | - | Sperian Eye & Face Protection, Inc QP EN 166 |

Conditions attached to the issue of this certificate:

- i) Marking and instructions have been assessed in the English language only. It is the Manufacturers/Authorised Representatives responsibility to obtain and supply language versions acceptable to the country where the product is to be sold.
- ii) Any changes to the product, technical file or quality manual/quality plan shall be immediately notified to INSPEC.
- iii) The Manufacturer/Authorised Representative shall comply at all times with INSPEC's Regulations governing CE Product Certification.
- iv) This Certificate remains the property of INSPEC and may be withdrawn if any of the conditions attached to its issue are not complied with.
- v) This certificate may be copied or reproduced by the certificate holder, complete and without omissions or additions, and in accordance with INSPEC's terms of business.
- vi) This certificate has been provided in accordance with our standard Terms of Business, which can be viewed at, and printed from:

<http://inspec-international.com/ToB.pdf>

If you have difficulty accessing the Terms of Business, you may contact us for a copy.

CERTIFICATION INDEX

Item	Status	Issued	Amendment
Certificate, Pages 1 – 4	Withdrawn	31/03/08	Initial Issue
Certificate Pages 1 to 4	Valid	110930	Product name change to Honeywell

CERTIFICATION SCHEDULE

Model	Temple colour	Lens colour and coating	Optical Class	Lens Filter	Options
1015370	Clear	Clear w / HC	1	2C-1.2	F
1015369		Clear w / FOG-BAN	1	2C-1.2	F
1015368	Gray	TSR Gray w / HC	1	5-2.5	F
1015367		TSR Gray w / FOG-BAN	1	5-2.5	F
1015350		I/O Silver w / HC	1	5-1.7	F

All lenses are polycarbonate

Key:

F - Low energy impact

CERTIFICATION/TEST REPORT RECEIPT FORM

DATE RECEIVED: September 30, 2014

PRODUCT: Honeywell A800

CERTIFICATION

TEST REPORT

SIGNATURES

Q.A. MANAGER: [Signature]

DIRECTOR QUALITY SYSTEMS: [Signature]

DIRECTOR R & D: [Signature]



EU-Konformitätserklärung

Der Hersteller oder sein in der EU als gesetzlicher Vertreter handelnder Lieferant:

Honeywell Safety Products Europe

Erklärt, dass die im Folgenden beschriebene Persönliche Schutzausrüstung die Richtlinien der Direktive des Europäischen Rates erfüllt 89/686/CEE:

Bezeichnung: A800, klar, FB

Referenz: 1015369

Standard(s): EN166

Für diese PSA gilt die folgende EU-Prüfbescheinigung Nr.:

EC 1790

Ausgestellt von:

INSPEC

56 Leslie Hough Way

Salford

M6 6AJ

Greater Manchester

United Kingdom

+44 (0)12 96 68 29 66

Ort, Datum: Manchester, 01/12/2014

Ausgestellt von: K J Warren

Abteilung: Augen- und Gesichtsschutz

HONEYWELL SAFETY PRODUCTS EUROPE

Immeuble Edison - ZI Paris Nord II - 33 rue des Vanesses

BP 55288 Villepinte - 95958 ROISSY CDG CEDEX

SAS au capital 17 750 000 € - Siret 348 867 307 00137

Tel. +331 4990 7979 - Fax +331 4990 7980

ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France

Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

www.honeywellsafety.com