

Product information

99 14 300 EAN

High Leverage Concreters' Nipper

High lever transmission

DIN ISO 9242



- 25 % less effort required compared to conventional concreters' nippers of the same size
- Extra-slim form for tying deep mounted steel rods
- To lace concrete reinforcing steel with binding wire from a roll
- Wire is twisted and cut in a single pass
- High-leverage joint, minimising strain, even when thick binding wires are used
- The high damping of the cutting stroke on cutting through the binding wire reduces the strain on tendons and muscles
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

General

Article No.	99 14 300 EAN
EAN	4003773039297
Pliers	bright zinc plated
Weight	499 g
Dimensions	300 x 49 x 24 mm
Standard	DIN ISO 9242
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities hard wire (diameter)	Ø 2.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting edge length mm	25.0 mm

technical change and errors excepted



